
Hour meters / timers, electromechanical





Accessories	Dimensions in mm [inch]		Order no.
Counter mounting fixture	for round counters with cut-out ø 53 [2.09"]	black	N510199

Suitable gaskets as well as further accessories can be found in the accessories section or in the accessories area of our website at: www.kuebler.com/accessories.

Technical data		
Electrical connection		flat pin 0.8 x 6.3 mm [0.031 x 0.25"]
Power consumption	AC	max. 0.4 VA
	12 V DC	max. 0.08 W
	48 V DC	max. 0.7 W
Rated voltages	AC (50 or 60 Hz)	115/230 V AC, ±10 %, 50/60 Hz
	DC	10 80 V DC
On time		100 %
Number of digits		6: 99999.9 h
Count mode		adding
Height of figures		3.5 mm [0.14"] heigh
Color of figures		white on black
Reset		no reset

Operating temperatur	e	-30°C +65°C [-22°F +185°F] (non-condensing)
Storage temperature		-40°C +85°C [-40°F +149°F]
Mounting position		any
Protection		IP65 (except the connections)
Housing		plastic PC (Polycarbonate)
Accuracy		< 0.02 % over the full range
Weight	HR 76.1 HR 76.2	56 g [1.98 oz] 54 g [1.91 oz]
EMC standards		EN 55011 class B EN 61000-6-2, EN 61000-6-3 EN 61326-1
Device safety	designed to protection class application area	EN 61010 part 1 2 pollution level 2
UL approval		file E128604



Hour meters / timers, electromechanical

