Control Cabinet Keys

for all standard cabinets and shut-off systems

00 11

- > for control cabinets and shut-off systems in the supply of gas, water and electricity
- > for technical installations in buildings, e.g. air conditioning and ventilation systems, shut-off valves, mains switchboards, etc.
- > with bit insert: slot 1.0 x 7 mm and cross recess PH2
- > with adapter for 1/4" bits chained to key
- > additional bit adapter for 1/4" bits inside one profile
- > Zinc die-casted

00 11 02

short version, total length 44 mm

00 11 03

long execution, total length 76 mm



	EAN	4- >	O 3	⊘ ∃	-O =	7,7
Article No.	4003773-	mm	mm	mm	mm	g
00 11 02	048947	44	5/6/8	9	3 - 5	65
00 11 03	041658	76	5/6/8	9	3 - 5	88

Profi-Key

for all standard shut-off systems

00 11

- key for heating, air conditioning, sanitary and building technology,e.g. for door and window handles or for radiator-bleeding
- > with bit insert: slot 1.0 x 7 mm and cross recess PH2
- > with adapter for 1/4" bits chained to key
- > additional bit adapter for 1/4" bits inside one profile
- > total length: 90 mm
- > Zinc die-casted



	EAN	←→	O 3			7,7
Article No.	4003773-	mm	mm	mm	mm	g
00 11 04	048954	90	5/7/8	9 - 10	6/7/8/9	86

Universal Key

for all standard cabinets and shut-off systems

00 11

- > for locking systems in electrical engineering, the supply of gas and water, air conditioning and ventilation systems, industry, technical installations in buildings, etc.
- > 9 different die-cast zinc key-profiles in 1 tool
- > with detachable chain and snap hook
- > total length: 90 mm
- > Zinc die-casted



Article No.	EAN 4003773-	4→ mm	<u>O</u> 3	<u></u>	O 3	○ ∃	2,7
Article No.	4005775-	111111	mm	mm	mm	mm	y
00 11 06	071334	90	5/6/7-8/9-10	7 / 8-9 / 10 - 11	3 - 5	6	220

Universal Key "Construction"

for all standard cabinets and shut-off systems

00 11

- > for locking systems in electrical engineering, the supply of gas and water, air conditioning and ventilation systems, industry, technical installations in buildings, etc.
- > 9 different die-cast zinc key-profiles in 1 tool
- > "Construction" version with plug-in, magnetically held support: catch for locks with profile cylinder hole and male square in steps
- > with bit adapter for 1/4" bits with magnet
- > with detachable chain and snap hook
- > total length: 157 / 95 mm
- > Zinc die-casted



00 11 06 V01

	EAN	←→	O]	⊘ ∃	-O E	○ ∃		44
Article No.	4003773-	mm	Ø mm	Ø mm	Ø mm	Ø mm	Ø mm	g
00 11 06 V01	075394	160	5/6/7-8/9-10	7 / 8 - 9 / 10 - 11	3 - 5	6	6/7/8/9/10	255