

## **In-Line Cartridge Fuse Holders** Fuse Holder > 155100

# 150 Series In-Line Holders for 2AG or 5×20mm Fuses

RoHS 🕫 c ঝ us



Agency

## **Product Characteristics**

Compatible Fuses	2AG or 5×20mm	
Electrical	This fuseholder, part number 150274, is intended for use with 2AG and 5 × 20mm fuses. Maximum current ratings are 5 amperes at 350V for the 2AG size fuses and 10 amperes at 350V for the 5 × 20mm size fuses.**	
Body	Black Nylon, UL94 V-0	
Terminals	Brass	
Wire	16 Awg size; Nominal o.d. 0.104"; color Red	
Lead Pull Test	Will withstand 10 lb. pull.	
Ambient Temperature	-40°C to +80°C*	

#### NOTES:

\* Refer to Fuseology for information on proper fuseholder re-rating.

\*\* If use above 32V, power must be turn off when changing the fuse

	Ordering Information	
cy File Number	Ordering Number	Packaging
E14721	01500274Z	Bulk Pack (100 Pcs)
	01500274LXN	Bulk Pack (50 Pcs)
	*01500274ZXU	Bulk Pack (5000 Pcs)

#### NOTES:


\* For unassembled Fuseholder, UL Recognition does not apply. \*\* Images are illustrative

## **Dimensions** [mm]

**Agency Approval** 

Agency

c **FL**us



### **Additional Information**





Samples

Disclaimer Notice - Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at: www.littelfuse.com/disclaimer-electronics.