




Circular connectors with threaded joint M16 acc. to IEC 61076-2-106, IP40/IP68





Crimp contact, contact bush gold-plated











\*a supporting strip

\*b unreeling direction

## **Environmental conditions**

Temperature range -40 °C/+85 °C

# Materials

Contact bush

CuSn, gold-plated – 0364 V109

## Mechanical data

Mating cycles $\geq$  500Insertion force/contact $\leq$  3.0 N<sup>1</sup>Withdrawal force/contact $\geq$  1.2 N<sup>1</sup><sup>1</sup> measured with a polished steel pin, nominal thickness 1.5 mm

## Connectable conductors for crimp area

Section	0,25–0,75 mm² (AWG 23–18)
Insulation diameter	≤ 1,8 mm

#### Electrical data (at Tamb 20 °C)

Contact resistance Rated current Rated voltage Further data ≤ 5 mΩ 5 A (T<sub>amb</sub> 40 °C) 250/320 V AC see suitable connector housing

### Associated products

Accessories	
<b>C</b> 0360	
C 036297	
🗗 KGV C	
🗗 WKV C	

☞ 0362 ☞ KFV ... C ☞ KV ...-8 C

Harnessing equipment CAW03 CZB03-0364 CZK03 VARICON 7000-DC CR VARICON 7000-RD CR VARICON 7000-RD CR VARICON 7000-RD

**1**036000

C 0363

🗗 KV ... C





Designation	Pole Number	PU (Pieces)	MDQ (Pieces)
0364 V109	1	10000	10000
0364 V109VP18	1	350	1750

Packaging:

on reel