#### 6000 Joker Ratcheting combination wrenches





ANTI-SLIP









**EAN:** 4013288167521 **Size:** 305x95x85 mm

 Part number:
 05020013001
 Weight:
 1932 g

 Article number:
 6000 Joker 11 Set 1
 Country of origin:
 CZ

Customs tariff 82041100

number:

- Practical holding function thanks to the metal plate in the jaw
- · Limit stop prevents any slipping
- The double-hex geometry reduces the risk of slipping
- Return angle of only 30°
- · With Take it easy tool finder: colour coding by size

High quality combination ratchet wrench set by Wera: everything that a wrench has to be able to do. And a whole lot more. Faster, better, stylish. Yes, a real Joker. The new generation of combination ratchet wrenches. 11-piece set in a robust pouch. Suitable for hexagon bolt heads or nuts. Comes with a holding function, thanks to the metal plate in the jaw, which reduces the risk of dropping nuts and bolts. The replaceable metal plate in the jaw secures nuts and bolts with its extra hard teeth and limits the danger of slipping. The integrated limit stop prevents any slipping down around the bolt head and allows higher torque to be applied. The double-hex geometry makes for a positive connection with nuts or bolts and reduces the risk of slipping. A return angle of only 30° at the open end prevents any time consuming flipping of the wrench during fastening jobs. The ratchet mechanism at the ring end, with an exceptional, fine-tooth mechanism — 80 teeth in all — enables flexibility even in very confined working spaces. The specially forged geometry provides for high torque transfer and strength. Manufactured out of high performance chrome molybdenum steel with a nickel-chrome coating for high corrosion protection. "Take it easy" Tool Finder with colour coding according to sizes.

#### 6000 Joker Ratcheting combination wrenches



#### Set contents:

## DEPOS AND FOR THE

# **6000 Joker**

05073268001 1 x 8 x 144 mm 05073270001 1 x 10 x 159 mm 05073271001 1 x 11 x 165 mm 05073272001 1 x 12 x 170.7 mm 05073273001 1 x 13 x 177 mm 05073274001 1 x 14 x 188 mm 05073275001 1 x 15 x 200 mm 05073276001 1 x 16 x 212 mm 05073277001 1 x 17 x 224 mm 05073278001 1 x 18 x 235 mm 05073279001 1 x 19 x 246 mm

### Joker open-ended wrench



When we began to think about open-ended wrenches, we asked ourselves: why does the wrench always have to be flipped over; why does it have an offset design; why does it slip off injuring fingers? The new design of the mouth resulted in a real "Joker"

trumps have been played.

that works even when all other

### **Holding function**



Joker's holding function means that nuts and bolts can be held in the jaw and easily positioned where they are needed. Fastening on to the thread can then be done quickly and safely, thanks to the innovative special stop-plate which holds fastener. No more time-wasting searches for dropped nuts and bolts! After applying and positioning the nut or bolt, fastening can begin immediately no additional tools required.

#### Integrated limit-stop



Constant re-positioning of the wrench? Difficulty holding fasteners in confined spaces? Easing off to avoid any risks of injury or fastener damage? That was yesterday. Today, the Joker prevents slipping off of the fastener head with its integrated limit-stop – no longer is the thumb needed to act as a depth stop. This makes applications much easier and allows signifi cantly more force to be applied during fastening jobs.

Web link

https://products.wera.de/en/joker\_6000\_joker\_ratcheting\_combination\_wrenches\_6000\_joker\_11\_set\_1.html

The ratcheting feature at the ring

end boasts an exceptional, fine

tooth mechanism - 80 teeth in all

- which provides greater flexibility,

even in very confined working

spaces.

#### 6000 Joker Ratcheting combination wrenches



#### Double-hex geometry

The Joker's clever double-hex geometry delivers a very positive connection with nuts or bolts — it's a perfect fit. And the exchangeable, hardened metal gripping plate in the Joker's mouth literally bites itself into the bolt, with its extremely hard tips. Both features combine to prevent slipping, even at higher torque.

#### Small return angle



Instead of 60°, the Joker only has a 30° return angle thanks to it's unique double-hex design. Along with the Joker's straight neck, this means that flipping the wrench has become a thing of the past. With the Joker, you can now loosen and tighten nuts and bolts, in situations where conventional tools fail. Particularly in confined spaces, where conventional openjawed wrenches cannot be used. The combination of limit stop and small return angle enables eff ective work, even on screw pipe connections.

#### Fine tooth mechanism



The ratcheting feature at the ring end boasts an exceptional, fine tooth mechanism – 80 teeth in all – which provides greater flexibility, even in very confined workingspaces.

#### "Take it easy" tool finder



Take it easy tool finder system - with profile and size colour-coding for quick and easy tool selection. Colour-coded system for hexagon drive screws (L-Keys, Zyklop bit sockets), external hex drive screws and nuts (Joker wrenches, Zyklop sockets and Zyklop bit sockets with holding function), and TORX® drive screws (L-Keys, Zyklop bit sockets).