### 3950 SPKL Multicolour HF L-key, metric, stainless steel, with holding function, 3 x 123 mm

L-Keys for Hexagon Socket Screws







EAN: 4013288224415 Size: 125x17x4 mm

Part number: 05022693001 Weight: 14 g Article number: 3950 SPKL Multicolour HF Country of origin:

> **Customs tariff** 82041100

number:

• Solution to the extraneous rust problem: fasten stainless screws with stainless tools

• Stainless L-keys prevent extraneous rust on stainless screws

· Hex-Plus allows socket head screws to live longer

- With holding function (HF) on the long arm to securely hold the screw on the tool
- The ball head on the long arm also allows offset use
- With Take it easy tool finder: colour coding by size
- All L-keys have a colour-coded, easy-grip hose sleeve for ergonomic and comfortable operation even at low temperatures











Premium stainless steel Wera L-key for hexagonal socket screws. Stainless steel prevents transmission of extraneous rust. The Hex-Plus profile offers larger contact surfaces in the screw head. The notch effect is reduced to a minimum and the destruction of the screw is nearly eliminated. With holding function for hexagonal socket screws on the long arm. With hexagonal ball tip at the long arm: The ballshaped tip profiles enable the tool shaft to be moved and pivoted relative to the screw axis which allows screwdriving "around the corner". "Take it easy" tool finder with colour coding by size. In a nearly wear-free L-key clip.

## 3950 SPKL Multicolour HF L-key, metric, stainless steel, with holding function, 3 x 123 mm

L-Keys for Hexagon Socket Screws



### Stainless L-keys



Stainless L-keys are hardened to the same strength as conventional (carbon) steel tools, and prevent extraenous rust forming.

#### Vacuum ice-hardened



The stainless steel tools from Wera are vacuum ice-hardened and have the hardness and strength needed for screw connections. There are no limitations to the industrial applications they are suitable for.

### L-keys with a thermoplastic sleeve



L-keys with a thermoplastic sleeve are manufactured out of easy-togrip, circular material. The sleeve ensures that work is safe and comfortable even at low temperatures. High corrosion protection features thanks to the special BlackLaser surface treatment. Colour coding and large stamp to enable the desired L-key to be easily located.

### **Hex-Plus**



Hexagon screws can endure a problem because the contact surfaces delivering the power from the conventional tool. transferred to the screw via very small surface areas. The consequence: the screw become damaged (rounding out). Hex-Plus tools have a greater contact surface that prevents this from happening! At the same time, as much as 20 % more torque can be applied. Good to know: Hex-Plus tools fit into every standard hexagon socket screw!

## With retaining function on long arm



The clamping of the screw is achieved by a flexible locking ball. The holding function is especially helpful in confined, hard-to-reach spaces, where there is no room for a second hand to secure the screw on the tool.

### Ball tip



The spherical drive profile means that it is possible to swivel the axis of the tool to that of the screw, and therefore enable angled, "around-the-corner" screwdriving jobs.

### Take it easy tool finder system



Take it easy tool finder system - with profile and size colour-coding for quick and easy tool selection. Colour-coded system for hexagon drive screws (L-Keys, Zyklop bit sockets), external hex drive screws and nuts (Joker wrenches, Zyklop sockets and Zyklop bit sockets with holding function), and TORX® drive screws (L-Keys, Zyklop bit sockets).

Web link

 $https://products.wera.de/en/l-keys\_l-keys\_for\_hexagon\_socket\_screws\_3950\_spkl\_multicolour\_hf.html$ 

Wera - 3950 SPKL Multicolour HF 05022693001 - 4013288224415

# 3950 SPKL Multicolour HF L-key, metric, stainless steel, with holding function, 3 x 123 mm $\,$

L-Keys for Hexagon Socket Screws



### Further versions in this product family:

	0	Å V		Å V	
	mm	mm	mm	inch	inch
05022693001	3.0	123	21	4 7/8"	27/32"
05022694001	4.0	137	24	5 3/8"	1"
05022695001	5.0	154	27	6 1/16"	1 1/16"
05022696001	6.0	172	31	6 3/4"	1 1/4"
05022697001	8.0	195	37	7 11/16"	1 7/16"
05022698001	10.0	224	42	9"	1 11/16"