2050 PH Screwdriver for Phillips screws for electronic applications, PH 0 x 60 mm

Series Kraftform Micro







EAN: Part number: Article number: 4013288031976 05118022001 2050 PH Micro Size: 157x13x13 mm Weight: 14 g Country of origin: CZ Customs tariff 82054000 number:













- Kraftform Micro screwdriver for cross-recess Phillips screws
- · Multi-component Kraftform Micro handle for fast and ergonomic screwdriving
- · Anti-roll feature and swivel cap for rapid twisting
- The Wera Black Point tip offers an exact fit and optimum corrosion protection
- Take it easy tool finder: colour coding according to profile and size

High quality Wera Micro screwdriver for precision mechanical jobs. Rapid twisting results from fixing the hand on the head and using the fast-turning zone just below. This makes time-consuming grip adjustments unnecessary. Power zones with integrated soft sections ensure the transfer of high loosening and tightening torque; a precision zone for the right rotation angle during fine adjustment work. The Black Point tip offers optimised corrosion protection and an exact fit. "Take it easy" tool finder with colour coding according to profiles and size stamp – for simple and rapid accessing of the required tool.

Kraftform Micro Handle

Series Kraftform Micro



The precision zone



Screwdriving jobs in electrical and precision engineering applications are often tedious and timeconsuming. We learned from users what is important for them: working speeds, torque, precision – and we then focused particularly on these issues.

A STATE

Multi-component screwdriver handle for ergonomic working.


The refined screwdriver for electronics technicians




The Kraftform Micro, with its three zones and their specific arrangement, satisfies these requirements perfectly. The freeturning cap that provides support for the hand works with these advantages, enabling quick and easy precision work.

The precision zone directly above the blade gives the user a better feel for the right rotation angle during fine adjustment work.

The power zone




The power zone has integrated soft zones near the blade tip to ensure high torque transfer for loosening or tightening screws without losing contact with the screw.



The fast-turning zone

The fast-turning zone just below the rotating cap allows rapid twisting.

Wera Black Point tip



The Wera Black Point tip and a refined hardening process ensure long service life of the tip, improved corrosion protection and an exact fit.

"Take it easy" Tool Finder



Screwdrivers with "Take it easy" tool finder: colour coding according to profile and size stamp.

Series Kraftform Micro



Further versions in this product family:

| | \mathbf{O} | | | Ø | |
|------------------------------|--------------|----|----|---------|--------|
| | | mm | mm | mm | inch |
| 05345290001 ^{1),2)} | PH 000 | 40 | 97 | 1.5/2.5 | 1 9/16 |
| 05118019001 ^{1),2)} | PH 00 | 40 | 97 | 1.8/2.5 | 1 9/16 |
| 051180200011) | PH 00 | 60 | 97 | 2.5 | 2 3/8 |
| 051180260013 | PH 0 | 40 | 97 | 3.0 | 1 9/16 |
| 05118022001 ³⁾ | PH 0 | 60 | 97 | 3.0 | 2 3/8 |
| 05118023001 | PH 1 | 60 | 97 | 4.0 | 2 3/8 |
| 05118024001 | PH 1 | 80 | 97 | 4.0 | 3 1/8 |

1) Optimised for Asian PH screws 2) On the output side, the blade is turned to a nominal length of 10 mm.

3) Size 0 modificated according to JCIS 0 (Japanese Camera Industrial Standard)