Needle-Nose Combination Pliers DIN ISO 5746

80

Small High Leverage Combination Pliers with pointed jaw For all common installation and repair work

- Handy use when working in confined areas thanks to slim head design and pointed jaws (anti-twist)
- Gripping surfaces with special convex contour on one side for secure gripping of flat parts
- Milled groove in the gripping area permits small parts such as nails, pins and bolts to be held and pulled
- > The reliable and diverse combination pliers when out and about
- > Easy cutting thanks to the high leverage joint
- > With cutting edges for soft, medium-hard and hard wire
- > Long service life and stable tips as the tool is forged from special high grade tool steel, manifold oil-hardened








Milled groove in the gripping area

Secure gripping of flat parts







							Cutting capacities				
Article No.	EAN 4003773-	∢ ► mm		Pliers	Head	Handles	Ømm	Ømm	Ømm	mm ²	۲ <u>۲</u> ۲
08 21 145	078951	145		black atramentized	polished	plastic coated	3.0	2.0	8.0	16	116
08 22 145	078968	145		black atramentized	polished	with multi-component grips	3.0	2.0	8.0	16	148
08 25 145	078975	145		chrome-plated		with multi-component grips	3.0	2.0	8.0	16	148
08 26 145	079361	145	₩₩ ♣ 1000 V @	chrome-plated		insulated with multi-component grips, VDE-tested	3.0	2.0	8.0	16	154