

Pneum.contact metal ID 10mm,female+valve



Image is for illustration purposes only. Please refer to product description.

Part number	09 14 000 6411
Specification	Pneum.contact metal ID 10mm,female+valve
HARTING eCatalogue	https://b2b.harting.com/09140006411

Identification

Category	Contacts
Type of contact	Pneumatic contact
Description of the contact	With shut-off Straight

Version

Gender	Female
Manufacturing process	Turned contacts

Technical characteristics

Limiting temperature	-40 ... +85 °C
Operating pressure	≤10 bar
Tube inner diameter	10 mm

Material properties

Material (contacts)	Brass
Material (seal)	NBR
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained



Pushing Performance
Since 1945

Material properties

REACH SVHC substances	Yes
REACH SVHC substances	Lead
ECHA SCIP number	b51e5b97-eeb5-438b-8538-f1771d43c17d
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel

Commercial data

Packaging size	10
Net weight	31.3 g
Country of origin	China
European customs tariff number	85366990
GTIN	5713140189379
ETIM	EC000796
eCl@ss	27440204 Contact for industrial connectors