

## Pneum.contact metal OD 8mm,female+valve



Image is for illustration purposes only. Please refer to product description.

Part number	09 14 000 6468
Specification	Pneum.contact metal OD 8mm,female+valve
HARTING eCatalogue	<a href="https://b2b.harting.com/09140006468">https://b2b.harting.com/09140006468</a>

### Identification

Category	Contacts
Type of contact	Pneumatic contact
Description of the contact	With shut-off Straight

### Version

Gender	Female
Manufacturing process	Turned contacts

### Technical characteristics

Limiting temperature	-20 ... +85 °C Tube outer diameter
Operating pressure	≤10 bar
Tube outer diameter	8 mm

### Material properties

Material (contacts)	Brass
Material (seal)	NBR
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained



**Pushing Performance**  
Since 1945

## Material properties

REACH SVHC substances	Yes
REACH SVHC substances	Lead
ECHA SCIP number	b51e5b97-eeb5-438b-8538-f1771d43c17d
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel

## Commercial data

Packaging size	10
Net weight	31.88 g
Country of origin	China
European customs tariff number	85366990
GTIN	5713140189225
ETIM	EC000796
eCl@ss	27440204 Contact for industrial connectors