

## SEK CAB FLAT NSH RND AWG28/7 14P 30,48m



Image is for illustration purposes only. Please refer to product description.

Part number	09 18 014 7008
Specification	SEK CAB FLAT NSH RND AWG28/7 14P 30,48m
HARTING eCatalogue	<a href="https://b2b.harting.com/09180147008">https://b2b.harting.com/09180147008</a>

### Identification

Category	System cabling
Element	Bulk cables
Specification	Not assembled
Type of cable	Copper cable (round)

### Version

Cable length	30.48 m
Number of cores	14
Core structure	AWG 28/7
Shielding	Unshielded

### Technical characteristics

Impedance	100 $\Omega$
Limiting temperature	-30 ... +75 °C unmoved -20 ... +75 °C moved
Conductor resistance @ 20 °C	$\leq 216 \Omega/\text{km}$

### Material properties

Material (cable)	PVC
Colour (cable)	Grey
RoHS	compliant
ELV status	compliant
China RoHS	e



**Pushing Performance**  
Since 1945

## Material properties

REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained

## Specifications and approvals

Specifications	UL 1581 UL PLCC, CL2
CE	Yes

## Commercial data

Packaging size	1
Net weight	1,710 g
Net weight	56 g/m
Country of origin	USA
European customs tariff number	85444993
GTIN	5713140024441
ETIM	EC003249
eCl@ss	27061801 Data and communication cable (copper)