

SEK CAB FLAT NSH RND AWG28/7 20P 30,48m



	Part number	09 18 020 7008
	Specification	SEK CAB FLAT NSH RND AWG28/7 20P 30,48m
	HARTING eCatalogue	https://b2b.harting.com/09180207008

Image is for illustration purposes only. Please refer to product description.

Identification

Category	System cabling	
Element	Bulk cables	
Specification	Not assembled	
Type of cable	Copper cable (round)	
Version		
Cable length	30.48 m	
Number of cores	20	
	20	
Core structure	AWG 28/7	

Technical characteristics

Impedance	100 Ω	
Limiting temperature	-30 +75 °C unmoved -20 +75 °C moved	
Conductor resistance @ 20 °C	≤216 Ω/km	
Material properties		
Material (cable)	PVC	
Colour (cable)	Grey	
RoHS	compliant	
ELV status	compliant	
China RoHS	e	

Page 1 / 2 | Creation date 2023-10-16 | Please note that the data specified here were taken as extracts from the online catalogue. Please refer to the user documentation for the complete and up-to-date information and data. Please also note that the user is responsible for validating functionality, conformity with applicable laws and directives, as well as for the electrical safety in the particular application. HARTING Electronics GmbH | Marienwerderstraße 3 | 32339 Espelkamp | Germany Phone +49 5772 47-97200 | electronics@HARTING.com | www.HARTING.com



Material properties

REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained

Specifications and approvals

Specifications	UL 1581 UL PLCC, CL2
CE	Yes

Commercial data

Packaging size	1
Net weight	69 g/m
Country of origin	Germany
European customs tariff number	85444993
GTIN	5713140024724
ETIM	EC003249
eCl@ss	27061801 Data and communication cable (copper)