



Leiterquerschnitt / wire gauge: 6mm² / AWG 10
 Abisolierlänge / stripping length: 9,5mm

		All Dimensions in mm Original Size DIN A 4		Techn. Character.		Nicht tolerierte Masse/ Free size tolerances		
						2:1	Han C Stiftkontakt gedreht 40A/ Han C male contact turned 40A versilbert / silver plated	
				Detail.	Dat. 09.11.10			ML
				Insp.				Be
				Stand.				
A				HARTING Electric GmbH & Co. KG D-32339 Espelkamp				
Mod.		Dat.		Name		TB 09 32 000 6108		
						Sub. TB 09 32 000 6108 v. 20.12.05		
						Blatt/ page		