

Smoke Detector RWM450 Wireless

Page 1 of 2



Technology

- · Q-mark certified by KRIWAN TESTZENTRUM
- Certified according to EN14604:2005/AC:2008
- Extended test according to vfdb14-01
- · Made in Germany
- One sensor for optical smoke detection and one sensor for temperature measurement
- Firmly installed 3V-lithium-battery with a lifespan of 12 years
- Frequency: 868,3 MHz
- · Several smoke detectors can be linked wirelessly (via radio)
- · Quick and clean assembly without drilling
- · Dimensions: 10,5 cm diameter, 4,0 cm height
- "88 dB" alarm
- CE according to 1772-CPR-150087
- · Alert for smoke + heat
- Radio range 400 m (+/- 10 %) in the open
- Repeater function

Operation and use

- · Bedrooms, children's rooms, corridors
- · Can also be used in kitchens
- Also suitable for recreational vehicles (e.g. mobile homes)
- May also be used in small businesses, provided that no grinding, gas, welding or sawing work is regularly carried out. This is because fine dust, exhaust gases and extreme temperature fluctuations could trigger false alarms.
- Tip: Check the functioning every four weeks
- In the event of one alarm being activated, all other alarms within range will also be set off

Variants

· Finish: pure white



Smoke Detector RWM450 Wireless

Page 2 of 2

Wireless smoke alarm device with heat alarm function