

HDC IP65

TE Internal #: 1-1102319-6

TE Internal Description: HB.24.STS.1.29.G

[View on TE.com >](#)



### Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2023 (233) Candidate List Declared Against: JAN 2023 (233) Does not contain REACH SVHC
Halogen Content	BFR/CFR/PVC Free, but Br/Cl >900 ppm in other sources.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

### Also in the Series | [HDC IP65](#)



Rectangular Connector Hoods & Bases  
(1258)


## Customers Also Bought



TE Part #1-2842115-0  
10P,2MM,BRK HDR,SRRT,2.8,0.38AU,  
TB W/CAP




TE Part #1-2842127-0  
20P,2MM,BRK HDR,DRVT,2.8,0.38AU,  
TB



TE Part #2842154-6  
12P,2MM,BRK HDR,DRRT,2.8,0.1AU,  
TB W/CAP



TE Part #1745013-1  
12 POS.RECEPTACLE CONNECTOR  
FOR 070 MULT



TE Part #1-1546073-2  
12POS 5.08MM TERMI-BLOK




TE Part #1-1658019-1  
MSB0.80PL25ASY28DP,-,10,VCTY




TE Part #1-87160-0  
09 MODI HDR SRST .156CL



TE Part #2355179-6  
6P,2MM,BRK HDR,SRVT,2.8,0.38AU,TB  
W/CAP



TE Part #1-2204456-0  
MB HD R/A PLUG 2P+2LP+2P+20S S  
EXTEND



TE Part #1-1971030-1  
Plug Housing for GIC 2.0 EV

## Documents

### Product Drawings

[HB.24.STS.1.29.G](#)

English