



Dynamic Series | Dynamic 2000 Series


TE Internal #: 1-1318114-9

Dynamic 2000 Series, Housing, Housing for Male Terminals, Wire-to-Wire, 20 Position, 2.5 mm [.098 in] Centerline, Crimp, 2 Row, Black

[View on TE.com >](#)

Connectors > PCB Connectors > Wire-to-Board Connectors > Wire-to-Board Connector Assemblies & Housings >

Receptacle and Tab Housing: 2.5 mm pitch, 250V



Connector Product Type: **Housing**

Connector & Housing Type: **Housing for Male Terminals**

Connector System: **Wire-to-Wire**

Number of Positions: **20**

Centerline (Pitch): **2.5 mm [.098 in]**

[All Receptacle and Tab Housing: 2.5 mm pitch, 250V \(54\)](#)

## Features

### Product Type Features

Connector Product Type	Housing
Connector & Housing Type	Housing for Male Terminals
Connector System	Wire-to-Wire
Sealable	No
Connector & Contact Terminates To	Wire & Cable

### Configuration Features

Number of Positions	20
Number of Rows	2

### Termination Features

Termination Method to Wire & Cable	Crimp
------------------------------------	-------

### Mechanical Attachment

--	--



Mating Retention	With
Connector Mounting Type	Panel Mount

### Housing Features

Centerline (Pitch)	2.5 mm [.098 in]
Housing Color	Black

### Dimensions

Row-to-Row Spacing	3.75 mm [.147 in]
--------------------	-------------------

### Usage Conditions

Operating Temperature Range	-55 – 105 °C [-67 – 221 °F]
-----------------------------	-----------------------------

### Operation/Application

Circuit Application	Signal
---------------------	--------

## Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2022 (223) Candidate List Declared Against: JAN 2022 (223) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

#### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>




## Compatible Parts




TE Part # CAT-D9934-A66  
Contact: Component To Wire ; 5A, 28-18 wire size, gold plated

## Also in the Series | Dynamic 2000 Series




Insertion & Extraction Tools(1)




PCB Connector Mounting(4)




PCB Headers & Receptacles(44)



PCB Terminal Blocks(23)



Wire-to-Board Connector Assemblies & Housings(54)



Wire-to-Board Connector Contacts(10)

## Customers Also Bought



TE Part #T1240100129-000  
H10B-TGH-PG29




TE Part #1-1318118-9  
DYNAMIC D-2100 REC HSG 20P



TE Part #4-1333205-8  
ANVIL, COMBINATION .090



TE Part #2119582-2  
Crimper, Insulation F Premium




TE Part #4-1333202-1  
ANVIL, COMBINATION .062




TE Part #9-2119582-5  
CRIMPER, INSULATION F PREMIUM




TE Part #2255146-1  
MINI SAHT D3000-M



TE Part #1722335-3  
BRACKET, COUNTER MOUNTING



TE Part #2844907-1  
POST, LOCKING



TE Part #2844908-1  
SCREW, LOCKING

## Documents

### Product Drawings

[DYNAMIC D-2100 TAB HSG 20P P/M](#)

English

### CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG\\_CVM\\_CVM\\_1-1318114-9\\_K.2d\\_dxf.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_1-1318114-9\\_K.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_1-1318114-9\\_K.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

### Datasheets & Catalog Pages

[1-1773732-4\\_DYNAMIC\\_SERIES\\_CATALOG\\_ENGLISH](#)

Japanese

[1-1773732-4\\_DYNAMIC\\_SERIES\\_CATALOG\\_ENGLISH](#)

English

### Product Specifications

[Dynamic Connector D-2000 Series](#)

Japanese



### Application Specification

Japanese

---

### Product Environmental Compliance

[MD\\_1-1318114-9\\_07112017640\\_dmtec](#)

English

[MD\\_1-1318114-9\\_07112017640\\_dmtec](#)

English