

**BN 22104****Screw plugs**

with metric thread

Polyamide PA 6

- Screw plug: polyamide PA 6 GF30
- Connecting thread: metric, as per EN 60423
- For secure sealing of unused threaded or clearance hole
- Temperature range: -40 °C / +100 °C
- Protection grade: IP54. When using an additionally mounted sealing ring IP66 / IP68 possible

Article#	d ₁	L	L ₁	d ₂	RAL	Color	Code
3691816	M12x1,5	6	10	15	7001	■	10.1215PA7001
3691804					7035	■	10.1215PA7035
3691814					9005	■	10.1215PA/SW
3691818	M16x1,5	6	10,5	20	7001	■	10.1615PA7001
3691819					7035	■	10.1615PA7035
3691812					9005	■	10.1615PA/SW
3691799	M20x1,5	6	10,5	24	7001	■	10.2015PA7001
3691797					7035	■	10.2015PA7035
3691813					9005	■	10.2015PA/SW
3691796	M25x1,5	8	13	30	7001	■	10.2515PA7001
3691809					7035	■	10.2515PA7035
3691801					9005	■	10.2515PA/SW
3691810	M32x1,5	8	13,5	37	7001	■	10.3215PA7001
3691815					7035	■	10.3215PA7035
3691807					9005	■	10.3215PA/SW
3691817	M40x1,5	8	14	46	7001	■	10.4015PA7001
3691811					7035	■	10.4015PA7035
3691805					9005	■	10.4015PA/SW
3691800	M50x1,5	10	16,5	56	7001	■	10.5015PA7001
3691806					7035	■	10.5015PA7035
3691803					9005	■	10.5015PA/SW
3691808	M63x1,5	12	17	70	7001	■	10.6315PA7001
3691798					7035	■	10.6315PA7035
3691802					9005	■	10.6315PA/SW