

ANSMANN Product Information



ANSMANN Powerline 4.2 Pro

- Charger for 1-4 AAA or AA rechargeable batteries incl. 1 USB charge output (5V / 1000mA)
- Suitable for NiMH rechargeable batteries
- Charge current can be individually set for each charge bay: 400mA, 600mA, 800mA when charging 1-4 rechargeable batteries 400mA, 600mA, 800mA, 1500mA, 1800mA when charging 1-2 rechargeable batteries
- Individually selectable charge program for each charge bay: CHARGE, DISCHARGE (Discharge Charge), REFRESH (Repeated discharging and charging to revitalise old rechargeable batteries), TEST (Charge discharge to determine capacity - charge)
- Simple identification of the respective selected charge program via the LCD display
- Microcontroller-controlled charging and monitoring of the charge status of each rechargeable battery.
- Individual call-up of the following parameters: Voltage (V) / Capacity (mAh/Ah) / Time (hh:mm) / Current (mA)
- Multiple overload protection for each rechargeable battery and automatic termination of the charge process
- Pulse maintenance charging δ reverse polarity protection

INFORMATION

Product namePowerPart No.1001-EAN-Code40136Customs tariff number85044Product contentPower

Powerline 4.2 Pro 1001-0079 4013674144624 85044055900 Powerline 4.2 Pro, mains adapter, operating instructions: Product Packing + Product Packing Unit 130 × 80 × 31 mm / 260 g 185 × 137 × 58 mm / 421 g 16 (390 × 294 × 262 mm)



ANSMANN Product Information

