



Value Masking Tape 101E

Product Data Sheet

December 2015
Supersedes: September 2014

Product Description

3M™ Value Masking Tape 101E is a tan coloured crepe paper masking tape for holding, bundling, sealing and non-critical masking applications where a pressure sensitive tape is needed.

Key Features

- Crepe paper backing.
- Rubber-based adhesive.
- Cost effective tape for indoor light duty applications.
- Temperature resistant up to 60°C for 30 minutes.

Physical Properties

Adhesive Type	Rubber
Backing Type	Crepe paper
Tape Colour	Tan

Performance Characteristics

Adhesion to Steel AFERA 5001	6 N/25mm
Tensile Strength AFERA 5004	84 N/25mm
Elongation at Break AFERA 5004	8 %
Thickness AFERA 5006	0.120 mm
Temperature Performance	60°C for 30 minutes

Storage

Store in clean and dry place.

Shelf Life

12 months from date of manufacture when stored in the original carton at 21°C & 50% Relative Humidity.

For Additional Information

To request additional product information or to arrange for sales Assistance, please see below for contact details.

Important Notice

All statements, technical information and recommendations contained in this document are based upon tests or experience that 3M believes are reliable. However, many factors beyond 3M's control can affect the use and performance of a 3M product in a particular application, including the conditions under which the product is used and the time and environmental conditions in which the product is expected to perform. Since these factors are uniquely within the user's knowledge and control, it is essential that the user evaluate the 3M product to determine whether it is fit for a particular purpose and suitable for the user's method or application. All questions of liability relating to this product are governed by the terms of the sale subject, where applicable, to the prevailing law

Values presented have been determined by standard test methods and are average values not to be used for specification purposes. Our recommendations on the use of our products are based on tests believed to be reliable but we would ask that you conduct your own tests to determine their suitability for your applications. This is because 3M cannot accept any responsibility or liability direct or consequential for loss or damage caused as a result of our recommendations

3M is a trademark the 3M Company.

**3M Svenska AB
Industri**

Bollstanäsvägen 3
191 89 Sollentuna

Tel: 08-92 21 00

Fax: 08-92 22 88

E-post:

[kundservice@mmm.co](mailto:kundservice@mmm.com)

[m](http://www.3m.se/tejp)

[www.3M.se/tejp](http://www.3m.se/tejp)

**3M a/s
Industri**

Hannemanns Allé 53
2300 København S

Tlf.: 43 48 01 00

Fax.: 43 20 15 65

E-mail:

[dkindustri@mmm.co](mailto:dkindustri@mmm.com)

[m](http://www.3m.dk)

www.3Mindustri.dk

**3M Norge AS
Avd. Industri**

Hvamveien 6
2013 Skjetten

Tel: 0 63 84

Fax: 63 84 17 88

E-post:

[Kundeservice@mmm.co](mailto:Kundeservice@mmm.com)

[m](http://www.3m.no)

www.3M.no/tape

**Suomen 3M Oy
Teollisuustuotteet**

PL 600

Keilaranta 6

02151 Espoo

Puh: 09-525 21

Fax: 09-525 2279

www.3M.fi/teollisuus