



Taper and deburring countersinker sets DIN 335 type C 90° HSS, HSSE-Co 5 and tungsten carbide K 20 in plastic case

	HSS	HSS	HSSE Co 5	HSS	HSS	TC
5-piece set of taper and deburring countersinkers DIN 335 type C 90° Ø 6,3 - 10,4 - 16,5 - 20,5 - 25,0 mm (Ø 16,5 mm = shank-Ø 10,0 mm)	102 154 RO	–	102 154 ERO	102 154 TRO	102 154 FRO	–
6-piece set of taper and deburring countersinkers DIN 335 type C 90° Ø 6,3 - 8,3 - 10,4 - 12,4 - 16,5 - 20,5 mm (Ø 16,5 mm = shank-Ø 10,0 mm)	102 152 RO	–	102 152 ERO	102 152 TRO	102 152 FRO	102 152 HMRO
17-piece set of taper and deburring countersinkers DIN 335 type C 90° Ø 4,3 - 5,0 - 6,0 - 6,3 - 7,0 - 8,0 - 8,3 - 10,0 - 10,4 - 11,5 - 12,4 - 15,0 - 16,5 - 19,0 - 20,5 - 23,0 - 25,0 mm (Ø 16,5 mm = shank-Ø 10,0 mm)	102 155 RO	–	–	–	–	–
6-piece set of taper and deburring countersinkers DIN 335 type C 90° Ø 6,3 - 10,4 - 16,5 - 20,5 - 25,0 mm (Ø 16,5 mm = shank-Ø 8,0 mm) + 1x cutting paste, 50 g	102 142	102 142 A	102 142 E	102 142 T	–	–

