

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1053002300](#)
Status: **Active**
Overview: [Nano-Fit Power Connectors](#)
Description: Nano-Fit Crimp Terminal, Female, 0.76µm Gold (Au) Plating, 20-22 AWG

Documents:

Drawing (PDF)	Test Summary 1053000000-TS-000 (PDF)
Product Specification PS-105300-100-001 (PDF)	RoHS Certificate of Compliance (PDF)
Packaging Specification PK-105300-100-000 (PDF)	Product Literature (PDF)

General

Product Family	Crimp Terminals
Series	105300
Application	Power, Wire-to-Board
Crimp Quality Equipment	Yes
Overview	Nano-Fit Power Connectors
Product Literature Order No	987651-1223
Product Name	Nano-Fit
UPC	889056003308

Physical

Durability (mating cycles max)	50
Gender	Female
Material - Metal	High Conductivity Copper
Material - Plating Mating	Gold over Nickel
Material - Plating Termination	Tin over Nickel
Net Weight	0.100/g
Packaging Type	Reel
Plating min - Mating	0.762µm
Plating min - Termination	2.540µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.60mm
Wire Size AWG	20, 22
Wire Size mm ²	0.30-0.50

Electrical

Current - Maximum per Contact	6.5A
Voltage - Maximum	250V AC (RMS)

Material Info

Reference - Drawing Numbers

Packaging Specification	PK-105300-100-000
Product Specification	PS-105300-100-001
Sales Drawing	SD-105300-100-000
Test Summary	1053000000-TS-000



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
ED/71/2019 (16 July
2019)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[105300 Series](#)

Use With

Nano-Fit Receptacle Housing [105307](#) ,
[105308](#)

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
-------------	-----------

Extraction Tool for Nano-Fit Power Connectors and Crimp Terminals, 20-26 AWG	638244600
--	---------------------------

Hand Crimp Tool for Nano-Fit Receptacle Terminals, 20-22 AWG UL1061 wire	638275600
--	---------------------------

and 22 AWG UL1007
wire
FineAdjust Applicator 639032400
for Nano-Fit
Terminals

Japan

Description	Product #
--------------------	------------------

S-1 Applicator for Nano-Fit Terminals, 20-22 AWG, UL1061 Wires	<u>2047483700</u>
---	-------------------

This document was generated on 09/19/2019

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION