


**W-Series  
WQV 120/2**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

**Product image****Klippon® Connect with clamping yoke Technology**

The high reliability and variety of designs of the terminal blocks with clamping yoke connections make planning easier and optimises operational safety. Klippon® Connect provides a proven response to a range of different requirements.

**General ordering data**

Type	WQV 120/2
Order No.	<a href="#">1063300000</a>
Version	W-Series, Cross-connector, For the terminals, No. of poles: 2
GTIN (EAN)	4008190025830
Qty.	5 pc(s).

**W-Series**  
**WQV 120/2**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Technical data****Dimensions and weights**

Width	10 mm	Width (inches)	0.394 inch
Height	44 mm	Height (inches)	1.732 inch
Depth	71.8 mm	Depth (inches)	2.827 inch
Net weight	143.4 g		

**Temperatures**

Continuous operating temp., min.	-50 °C	Continuous operating temp., max.	100 °C
----------------------------------	--------	----------------------------------	--------

**Material data**

Material	PA 66	Colour code	Silver grey
UL 94 flammability rating	V-2		

**System specifications**

Version	For the terminals	Tightening torque (cross-connector)	2...3 Nm
Rail	none		

**Additional technical data**

Installation advice	Direct mounting	Type of fixing	when screwed in
---------------------	-----------------	----------------	-----------------

**Cross-connector**

No. of cross-connected terminals	2	Rated current, 2-pole	269 A
Rated current, multi-pole	269 A	Type	Cross-connector

**Dimensions**

Pitch in mm (P)	32 mm
-----------------	-------

**Rating data**

Rated current	269 A
---------------	-------

**Classifications**

ETIM 3.0	EC000489	ETIM 4.0	EC000489
ETIM 5.0	EC000489	ETIM 6.0	EC000489
UNSPSC	30-21-18-01	eClass 5.1	27-14-11-40
eClass 6.2	27-14-11-40	eClass 7.1	27-14-11-40
eClass 8.1	27-14-11-40	eClass 9.0	27-14-11-40
eClass 9.1	27-14-11-40		

**Approvals**

ROHS	Conform
------	---------

**Downloads**

Brochure/Catalogue	<a href="#">CAT 1 TERM 16/17 EN</a>
Engineering Data	<a href="#">EPLAN, WSCAD, Zuken E3.S</a>
Engineering Data	<a href="#">STEP</a>

Creation date March 1, 2019 4:51:11 PM CET

**Data sheet****W-Series  
WQV 120/2**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

**Accessories****Cutting and notching tools for cross-connections**

- for Weidmüller Z-Series cross-connections
- for cross-connections from WQV 2.5 to WQV 35
- for cross-connection window of the terminal WSI 6

**General ordering data**

Type	Order No.	Version	GTIN (EAN)	Qty.
WAW 1	<a href="#">9004500000</a>	Miscellaneous tools	4008190053925	1 pc(s).
NEUTRAL				