



EMPTY ENCLOSURE

TK PS 2518-16-tm



TK PS 2518-16-tm

Empty enclosure

CUSTOMIZE

254 x 180 x 165 mm
Article number: 10700801

Empty enclosure, Base: polystyrene, Grey, similar to RAL 7035, Cover: polycarbonate, transparent

with metric knockouts



Technical data

Measures

Width:	254 mm
Length:	180 mm
Height:	165 mm
Inner height:	150 mm

Material:

Box:	Polystyrene, light grey, similar to RAL 7035
Cover:	Polycarbonate, transparent
Sealing:	Polyurethane
Cover screw:	Polyamide 6, fiber-glass reinforced
material:	polystyrene

Accessory

ASS-gro - External hinge set

HBA - Mounting material

MPS-KRI - Mounting plate

NS 35-216 - Standard rail

TK ABL - External fixing lugs kit

TK MPI-2518 - Mounting plate

Environmental attributes

Ambient temperature (min.):	-25 °C
Ambient temperature (max.):	40 °C
Ambient temperature (24 h):	35 °C
Max. rel. humidity at 25° C (short term):	95%
Max. rel. humidity at 40° C:	50%



EMPTY ENCLOSURE

TK PS 2518-16-tm

Other attributes

Ingress protection:	IP66 - acc. EN 60529 / DIN VDE 0470-1
Impact resistance:	IK07 acc. DIN EN 5012 / VDE 0470 Part 100
Protection class:	II - isolate protection acc. VDE 0106
Rated insulation voltage AC:	690 V
Rated insulation voltage DC:	1000 V
Heavy metals-free:	Yes
PVC-free:	Yes
Silicone-free:	Yes
Fitted for outdoor application:	No
Combustion behaviour acc. to UL 94:	HB/V-2 acc. UL 94
Combustion behaviour acc. to VDE:	650°C acc. VDE 0471/ EN 60695
sealable:	Yes
weatherproof:	No
Cable entries:	Yes
Cover screw torque:	1.2 N m
Domed fastener torque:	1.5 N m
External hinge torque:	1.5 N m