

## Sets of screw-hole punches in plastic cases

		Article no.
Set 1	11 - piece set of screw-hole punches 6 screw-hole punches Ø 15,2 (PG 9) - 18,6 (PG 11) - 20,4 (M 20 / PG 13,5) - 22,5 (PG 16) - 28,3 (PG 21) + 32,0 mm + 1 tube and sheet drill HSS size 1 + 1 cutting paste 30 g + 2 draw-in bolts MF 10 x 1,0 x 45, grade 12.9 + 1 draw-in bolt MF 12 x 1,5 x 55, grade 12.9	109 002
Set 2	13 - piece set of screw-hole punches 8 screw-hole punches Ø 15,2 (PG 9) - 18,6 (PG 11) - 20,4 (M 20 / PG 13,5) - 22,5 (PG 16) - 28,3 (PG 21) 37,0 (PG 29) - 47,0 (PG 36) + 54,0 mm (PG 42) + 1 tube and sheet drill HSS size 2 + 1 cutting paste 30 g + 1 draw-in bolt MF 10 x 1,0 x 45, grade 12.9 + 1 draw-in bolt MF 12 x 1,5 x 55, grade 12.9 + 1 draw-in bolt MF 16 x 1,5 x 60, grade 12.9	109 003
Set 3	10 - piece set of screw-hole punches 5 screw-hole punches Ø 16,5 (M 16) - 20,4 (M 20 / PG 13,5) - 25,4 (M 25) - 32,5 (M 32) + 40,5 mm (M 40) + 1 tube and sheet drill HSS size 2 + 1 cutting paste 30 g + 1 draw-in bolt MF 10 x 1,0 x 45, grade 12.9 + 1 draw-in bolt MF 12 x 1,5 x 55, grade 12.9 + 1 draw-in bolt MF 16 x 1,5 x 60, grade 12.9	109 006
Set 4	12 - piece set of screw-hole punches 7 screw-hole punches Ø 16,5 (M 16) - 20,4 (M 20 / PG 13,5) - 25,4 (M 25) - 32,5 (M 32) - 40,5 (M 40) 50,5 (M 50) + 63,5 mm (M 63) + 1 tube and sheet drill HSS size 2 + 1 cutting paste 30 g + 1 draw-in bolt MF 10 x 1,0 x 45, grade 12.9 + 1 draw-in bolt MF 12 x 1,5 x 55, grade 12.9 + 1 draw-in bolt MF 16 x 1,5 x 60, grade 12.9	109 008

