



HP Pro c640 Chromebook

The powerful, sleek, and secure Chromebook for business-class productivity

Effortlessly, efficiently run the projects and meetings of your day with the fast and secure HP Pro c640 Chromebook. Inside the stylish aluminum exterior lies enhanced performance and privacy with an Intel® processor¹ and an HP Privacy Camera.



Polished, pro-class portability

- Exude class wherever the day takes you with an aluminum-exterior device that's stylish and easy to carry. It's also built to last, undergoes MIL-STD 810H testing³, and has a backlit keyboard that resists spills up to 350 ml (12 oz) of water.⁴

Secure inside and out

- Deter remote camera hacking with the HP Privacy Camera. Login quickly and securely with the optional fingerprint sensor.² Keep your device safe, secure, and always up to date with the automatic updates and built-in anti-virus protection of Chrome OS.

Built for seamless, anytime productivity and collaboration

- Collaborate and work in multiple tabs with an Intel® processor¹, 180° lie-flat chassis, and built-in webcam and audio. Connect virtually anywhere with HP Extended Range Wireless LAN.⁶
- Never wonder if someone is watching you with the added peace of mind that comes from the integrated HP Privacy Camera, which has a physical shutter to protect you from malicious surveillance.
- Skip the passwords and enjoy fast, easy logins with the optional, integrated fingerprint sensor.²
- Spend more time getting your work done instead of looking for an outlet with long battery life and HP Fast Charge, which recharges the battery to 90% in 90 minutes.⁷
- Enjoy greater speed and stability on crowded networks with Wi-Fi 6 and HP Extended Range Wireless LAN.^{6,8,9}
- Work without worry with Chrome OS's multi-layered safeguards, including automatic updates through June 2028, virus protection, sandboxing, encryption and Verified Boot.⁵
- Charge up your Chromebook and USB-C® accessories with two USB-C® ports. Expand to an optional HP USB-C® dock to connect to a wired network and access USB-A accessories.¹⁰
- Breathe easy with an IT investment that is supported by our standard limited warranty. Extend your protection to cover accidents, travel, next-business day needs, and more with optional HP Care Pack services.¹¹
- Make the most of your collaboration and virtual meetings with powerful Audio by B&O, an integrated wide view angle HD camera to show the whole room to remote attendees, and HDMI port to easily add a projector without using dongles.
- Use multiple tabs and apps simultaneously and store files locally on a Chromebook built for the enterprise with up to 16 GB memory and 128 GB eMMC storage. Enjoy a familiar Android™ mobile app experience with the optional touchscreen.^{2,12,13}

HP Pro c640 Chromebook Specifications Table



Available Operating Systems	Chrome OS™ 64
Processor family ⁴	Intel® Pentium® Gold processor; 10th Generation Intel® Core™ i7 processor (i7-10610U); 10th Generation Intel® Core™ i5 processor (i5-10310U); 10th Generation Intel® Core™ i3 processor (i3-10110U)
Available Processors ^{1,2,3,4}	Intel® Core™ i7-10610U processor with Intel® UHD Graphics (1.8 GHz base frequency, up to 4.9 GHz with Intel® Turbo Boost Technology, 8 MB L3 cache, 4 cores) Intel® Core™ i5-10310U processor with Intel® UHD Graphics (1.6 GHz base frequency, up to 4.4 GHz with Intel® Turbo Boost Technology, 6 MB L3 cache, 4 cores) Intel® Core™ i3-10110U processor with Intel® UHD Graphics (2.1 GHz base frequency, up to 4.1 GHz with Intel® Turbo Boost Technology, 4 MB L3 cache, 2 cores) Intel® Pentium® Gold 6405U processor with Intel® UHD Graphics (2.4 GHz base frequency, 2 MB L3 cache, 2 cores)
Display size (diagonal)	14"
Maximum memory	16 GB LPDDR4-2666 SDRAM Onboard memory. Supports Dual Channel Memory.
Internal storage	32 GB up to 128 GB eMMC 5.0 ⁵
Optical drive	Not included
Display ^{9,12}	14" diagonal HD SVA anti-glare On-Cell micro-edge WLED-backlit touch screen, 220 nits, 45% NTSC (1366 x 768) 14" diagonal FHD IPS anti-glare On-Cell micro-edge WLED-backlit touch screen, 250 nits, 45% NTSC (1920 x 1080) 14" diagonal FHD IPS anti-glare micro-edge WLED-backlit, 250 nits, 45% NTSC (1920 x 1080) 14" diagonal HD SVA anti-glare micro-edge WLED-backlit, 220 nits, 45% NTSC (1366 x 768)
Available Graphics	Integrated: Intel® UHD Graphics ⁹ (Support HD Decode, DX12, and HDMI 1.4b.)
Audio	Audio by B&O, dual stereo speakers
Wireless technologies ^{7,8}	Intel® AX201 Wi-Fi 6 (2x2) and Bluetooth® 5 Combo, non-vPro™ (HP Extended Range Wireless Lan, MU-MIMO and Chromecast support)
Expansion slots	1 microSD; 1 multi-format digital media reader (Supports SD, SDHC, SDXC.)
Ports and Connectors	2 USB 3.1 Type-C® Gen 1 (Power delivery, DisplayPort™); 2 USB 3.1 Gen 1; 1 headphone/microphone combo; 1 HDMI 1.4 (HDMI cable sold separately.)
Available Keyboards	Full-size textured island-style Chrome keyboard, pike silver, spill resistant; Full-size 3-coat painted island-style Chrome keyboard, backlit, pike silver, spill resistant; Full-size 3-coat painted island-style Chrome keyboard for FPS, backlit, pike silver, spill resistant ^{10,11}
Available Pointing Devices	Touchpad with multi-touch gesture support, taps enabled as default
Camera ^{9,10}	720p HD camera; HD Privacy webcam
Software ¹³	Chrome Enterprise Upgrade; Google G Suite; Google Play Store
Security management ^{14,15}	Nano Security lock slot; Google H1 Security Chip
Fingerprint reader	Fingerprint reader (select models)
Power ¹⁸	HP Smart 65 W USB Type-C® adapter; HP Smart 45 W USB Type-C® adapter
Battery type ¹⁷	HP Long Life 3-cell, 60 Wh Li-ion Battery is internal and not replaceable by customer. Serviceable by warranty. Fast charging 90% in 90 minutes.
Battery life ¹⁶	Up to 12 hours
Dimensions	12.8 x 8.07 x 0.65 in; 32.5 x 20.5 x 1.65 cm
Weight	Starting at 3.35 lb; Starting at 1.5 kg
Energy efficiency compliance ²⁰	ENERGY STAR® certified; EPEAT® registered where applicable. EPEAT registration varies by country. See www.epeat.net for registration status by country.
Environmental specifications ²¹	Low halogen; TCO 8.0 Certified
Warranty ¹⁹	HP Services offers 1 year and 90 day limited warranty options depending on country. Batteries have a default 1 year limited warranty. On-site service and extended coverage is also available. HP Care Pack Services are optional extended service contracts that go beyond the standard limited warranties. Service levels and response times for HP Care Packs may vary depending on your geographic location. To choose the right level of service for your HP product, use the HP Care Pack Services Lookup Tool at: http://www.hp.com/go/cpc

HP Pro c640 Chromebook

Accessories and services (not included)

HP 45W USB-C LC Power Adapter



Power and charge your HP Chromebook¹ from its USB-C™ port with the HP 45W USB-C LC Power Adapter.
Product number: 1MZ01AA

HP Recycled Series 15.6-inch Top Load



Helps protect the planet and your notebook¹ and daily essentials with the stylish, durable HP Recycled Series 15.6" Top Load, a carryall made from recycled plastics.²
Product number: 5KN29AA

HP Sure Key Cable Lock



Take the guess work out of securing your notebook, display, dock, and accessories with the removable, interchangeable heads of the HP Sure Key Cable Lock.¹
Product number: 6UW42AA

HP USB-C Travel Hub G2



Easily expand your laptop's connectivity when working on the go with HP USB-C Travel Hub G2.¹ Add an extra display² and your accessories, charge your laptop and phone—all with one USB-C™ cable connection.
Product number: 7PJ38AA

HP Slim USB Keyboard and Mouse



Work smart and maximize your workspace with the stylish HP Slim USB Keyboard and Mouse, designed to complement the 2015 class of HP Business PCs.
Product number: T6T83AA

Additional Services (Not included)



HP Care Pack

U9DP6E - HP 3 year Pickup and Return Notebook Only Service
U9DP8E - HP 3 year Next business day onsite Notebook Only Service
U9DQ0E - HP 3 year Next business day onsite with Accidental Damage Protection Gen 2 Notebook Only Service

HP Pro c640 Chromebook

Messaging Footnotes

- ¹ Multi-Core is designed to improve performance of certain software products. Not all customers or software applications will necessarily benefit from use of this technology. Performance and clock frequency will vary depending on application workload and your hardware and software configurations. Intel's numbering, branding and/or naming is not a measurement of higher performance.
- ² Optional feature that must be configured at the time of purchase.
- ³ MIL STD 810H testing is not intended to demonstrate fitness for U.S. Department of Defense contract requirements or for military use. Test results are not a guarantee of future performance under these test conditions. Accidental damage requires an optional HP Accidental Damage Protection Care Pack.
- ⁴ HP Total Test Process testing is not a guarantee of future performance under these test conditions. Any accidental damage requires an optional HP Accidental Damage Protection Care Pack.
- ⁵ See <https://support.google.com/chrome/a/answer/6220366?hl=en> for more information.
- ⁶ Based on internal testing vs. previous generation product with 802.11ac wireless LAN module.
- ⁷ Recharges the battery up to 90% within 90 minutes when the system is off or in standby mode, when used with the power adapter provided with the notebook, and no external devices are connected. After charging has reached 90% capacity, charging speed will return to normal. Charging time may vary +/-10% due to System tolerance.
- ⁸ Wireless access point and internet service required and sold separately. Availability of public wireless access points limited. Wi-Fi 6 is backwards compatible with prior 802.11 specs. The specifications for Wi-Fi 6 (802.11ax) are draft and are not final. If the final specifications differ from the draft specifications, it may affect the ability of the notebook to communicate with other 802.11ax devices.
- ⁹ Wi-Fi® supporting gigabit speeds is achievable with Wi-Fi 6 (802.11ax) when transferring files between two devices connected to the same router. Requires a wireless router, sold separately, that supports 160MHz channels. Based on internal testing vs. previous generation product with 802.11ac wireless LAN module.
- ¹⁰ Sold separately or as an optional feature.
- ¹¹ Sold separately. Service levels and response times for HP Care Packs may vary depending on your geographic location. Service starts on date of hardware purchase. Restrictions and limitations apply. For details, visit www.hp.com/go/cpc. HP services are governed by the applicable HP terms and conditions of service provided or indicated to Customer at the time of purchase. Customer may have additional statutory rights according to applicable local laws, and such rights are not in any way affected by the HP terms and conditions of service or the HP Limited Warranty provided with your HP Product.
- ¹² Internet access required and sold separately. Some apps may require purchase.
- ¹³ For storage drives, GB = 1 billion bytes. Actual formatted capacity is less. Up to 8.1 GB is not user available.

Technical Specifications Footnotes

- ¹ Multicore is designed to improve performance of certain software products. Not all customers or software applications will necessarily benefit from use of this technology. Performance and clock frequency will vary depending on application workload and your hardware and software configurations. Intel's numbering, branding and/or naming is not a measurement of higher performance.
- ² Processor speed denotes maximum performance mode; processors will run at lower speeds in battery optimization mode.
- ³ Intel® Turbo Boost performance varies depending on hardware, software and overall system configuration. See www.intel.com/technology/turboboost for more information.
- ⁴ In accordance with Microsoft's support policy, HP does not support the Windows 8 or Windows 7 operating system on products configured with Intel and AMD 7th generation and forward processors or provide any Windows 8 or Windows 7 drivers on <http://www.support.hp.com>.
- ⁵ For storage drives, GB = 1 billion bytes. Actual formatted capacity is less. Up to 5.1 GB is not user available.
- ⁶ Google Drive offer is tied to this device and is non-transferable. If this device is returned, the extra storage will be revoked. In order to redeem this offer, you will need to be on Chrome OS™ 23 or later. Internet access is required and not included. Additional information about storage plan refunds, renewals, cancellations and expiration is available at the Google website: <https://support.google.com/chromebook/answer/2703646?hl=en>.
- ⁷ Wireless access point and internet service required and sold separately. Availability of public wireless access points limited.
- ⁸ Chromecast must be purchased separately.
- ⁹ HD content required to view HD images.
- ¹⁰ HD Privacy webcam is sold separately or as an optional feature.
- ¹¹ Backlit keyboard is an optional feature.
- ¹² Resolutions are dependent upon monitor capability, and resolution and color depth settings.
- ¹³ Chrome Enterprise Upgrade is sold separately and requires one-time setup, subscription, Google Admin Console, and your organization's domain. Please see <https://support.google.com/a/answer/60216>.
- ¹⁴ Lock is sold separately.
- ¹⁵ HP Fingerprint Reader is an optional feature and requires configuration at purchase.
- ¹⁶ Testing conducted by HP using Google Chrome OS power_LoadTest. Battery life will vary and the maximum capacity of the battery will naturally decrease with time and usage and battery optimization activation. See <http://www.chromium.org/chromium-os/testing/power-testing> for test details.
- ¹⁷ Recharges the battery up to 90% within 90 minutes when the system is off or in standby mode. Power adapter with a minimum capacity of 65 watts is required. After charging has reached 50% capacity, charging will return to normal. Charging time may vary +/-10% due to System tolerance.
- ¹⁸ Availability may vary by country.
- ¹⁹ HP Care Packs are sold separately. Service levels and response times for HP Care Packs may vary depending on your geographic location. Service starts on date of hardware purchase. Restrictions and limitations apply. For details, visit www.hp.com/go/cpc. HP services are governed by the applicable HP terms and conditions of service provided or indicated to Customer at the time of purchase. Customer may have additional statutory rights according to applicable local laws, and such rights are not in any way affected by the HP terms and conditions of service or the HP Limited Warranty provided with your HP Product.
- ²⁰ Based on US EPEAT® registration according to IEEE 1680.1-2018 EPEAT®. Status varies by country. Visit www.epeat.net for more information.
- ²¹ External power supplies, power cords, cables and peripherals are not Low Halogen. Service parts obtained after purchase may not be Low Halogen.

Sign up for updates hp.com/go/getupdated

© Copyright 2020 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products are set forth in the express limited warranty statements accompanying such products. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

Intel, Core, Celeron and Intel vPro are trademarks or registered trademarks of Intel Corporation or its subsidiaries in the United States and other countries. Bluetooth is a trademark owned by its proprietor and used by HP Inc. under license. DisplayPort™ and the DisplayPort™ logo are trademarks owned by the Video Electronics Standards Association (VESA®) in the United States and other countries. USB Type-C® and USB-C® are registered trademarks of USB Implementers Forum. SDXC is a registered trademark of SD-3C in the United States, other countries or both. ENERGY STAR is a registered trademark of the U.S. Environmental Protection Agency. © 2020 Google LLC All rights reserved. Google and the Google Logo are registered trademarks of Google LLC.

4aa7-6761, 2020 May 13

