ROLINE HDMI High Speed Cable, M/M, 10 m

Product No.		
Manufacturer		
Manufacturer No.		
EAN (single piece)		

11.04.5576 ROLINE 11.04.5576 7611990188024







HDMI (High-Definition Multimedia Interface) supports standard, enhanced, or high-definition video, plus multi-channel digital audio on a single cable.

It transmits all ATSC HDTV standards and supports 8-channel, 192kHz, uncompressed digital audio and all currently-available compressed formats (such as Dolby Digital and DTS). HDMI High Speed adds additional support for new lossless digital audio formats Dolby® TrueHD and DTS-HD Master AudioT with bandwidth to spare to accommodate future enhancements and requirements.

• By delivering crystal-clear, all-digital audio and video via a single cable, HDMI dramatically simplifies cabling and helps provide consumers with the highest-quality home theater experience.

- Maximum resolution: 1920x1080 @60Hz
- HDMI High Speed increases single-link bandwidth to 340 MHz (10.2 Gbit/s)
- HDMI High Speed supports 10-bit, 12-bit and 16-bit (RGB or YCbCr) color depths, for stunning rendering of over one billion colors in unprecedented detail
- ROLINE cable with high quality shielding
- Colour: black

Technical specifications			
Manufacturer	ROLINE		

Product group	Cable
Product type	HDMI High Speed Cable
Colour	black
Length	10 m
Transfer quality	HDMI High Speed
Max. resolution	1920 x 1080 / 1920 x 1200 @60Hz (2K, Full HD)
side 1 connector	HDMI 19 Male
side 2 connector	HDMI 19 Male
Side 1 Connector Type	HDMI Type A
Side 1 Connector Gender	Male
Side 2 Connector Type	HDMI Type A
Side 2 Connector Gender	Male
Area of application	External
Cable shielding	Screened
Technical particularity	HDMI High Speed
Weight	607.5 g
Height of packaging (single piece)	30 mm
Width of packaging (single piece)	160 mm
Depth of packaging (single piece)	150 mm
Package weight (single piece)	0.541 kg