


## Spur wheels | other | Spur wheels



Made of 100% polyacetal (POM) for a low-noise and shock-free transfer.

Service temperature: up to 95°C

Max. tooth load: 35 N/mm<sup>2</sup>

Tolerances: 140 DIN 16901

Pressure angle: 20°

Material: POM

Colour: natural

X = number of teeth / M = module

Part no.	M	X	B	C	D	E	F
1040027	0,5	15	7,5	3	6	3	10
1040028	0,5	18	9,0	4	8	3	10
1040029	0,5	20	10,0	4	8	3	10
1040030	0,5	25	12,5	4	10	3	10
1040031	0,	30	15,0	4	12	3	10
1040032	0,5	35	17,5	4	12	3	10
1040033	0,5	40	20,0	4	12	3	10
1040034	0,5	45	22,5	4	12	3	10
1040035	0,5	48	24,0	6	15	3	10
1040036	0,5	50	25,0	6	15	3	10
1040037	0,5	60	30,0	6	15	3	10
1040038	0,5	72	36,0	6	15	3	10
1040039	0,5	96	48,0	6	15	3	10
1040040	0,5	120	60,0	6	15	3	10
1040001	1	12	12,0	4	9	8	16
1040002	1	15	15,0	4	9	8	16
1040003	1	18	18,0	4	9	8	16
1040004	1	20	20,0	6	12	8	16
1040005	1	21	21,0	6	12	8	16
1040006	1	24	24,0	6	12	8	16
1040007	1	28	28,0	6	12	8	16
1040008	1	30	30,0	6	12	8	16
1040009	1	32	32,0	6	12	8	16
1040010	1	35	35,0	8	16	8	20
1040011	1	40	40,0	8	16	8	20
1040012	1	45	45,0	8	16	8	20
1040013	1	50	50,0	8	16	8	20
1040014	1	60	60,0	8	16	8	20
1040041	1,5	12	18,0	6	14	12	23
1040042	1,5	15	22,5	6	14	12	23
1040043	1,5	18	27,0	8	17	12	23
1040044	1,5	20	30,0	8	17	12	23