

Data sheet

Order number: 112002

wall mounting socket outlet Quick-Connect

Ampere	32A
Poles	5p (3p+N+PE)
Orientation	6 h
Voltage	200/346 up to 240/415V
Frequency	50 and 60Hz
Protection	IP44
Color Code	RAL 3000 red (Hinged Cover)
Connection Design	screwless spring terminals as cage clamp with Kontext-contact button
Contact carrier	moulded in the collar, contacts are brass
Material of enclosure	housing material Polyamide Polyamide

