## **LED** machine luminaire

## SPOT LED 003 - MCXFL 3 S 112459004-00082950



ENGINEER OF LIGHT.



fitted with

work equipment connected load power consumption system of protection class of protection technology usage luminaire body lamp cover

balance of articulation joints

weight (net) mains lead fastening

special features

3 x Light-emitting diode

light colour daylight white, 5500-6000 K, Color Rendering

Index (CRI)=72

Energy efficiency category A+

without 24 V: AC/DC approx. 6 W IP 67 Ш

switchable without switch

aluminium, anodised, black

glass screen friction approx. 0.7 kg

approx. 3.0 m; with free stranded wires


screw-down flange, magnetic base (accessory), table clamp

(accessory), wall bracket (accessory) Spot with a 10° angle of radiation

## illuminance

4086 lx Emax: Emin: 27500 lx 440 lx 30 cm

measuring conditions: d=50cm



## luminous intensity

