Surface-mounted luminaire

MACH LED PLUS - MQAL 60 S 113124000-00611855



fitted with

work equipment connected load power consumption luminous flux luminous efficacy light distribution **Beam Angle** light colour color rendering index (CRI) system of protection class of protection technology usage luminaire body lamp cover weight (net) mains supply design

fastening dimension special features Waldmann W

ENGINEER OF LIGHT.


60 x LED Energy efficiency category A+ without 18-30 V; DC approx. 30 W approx. 2300 lm approx. 77 lm/W direct 80°/100° neutral white, approx. 5000 K > 80 IP 67 Ш switchable external aluminium, anodised, aluminium coloured anodised screen, clear approx. 2.6 kg built-in plug Serie_763 mounted version L-angle, clamp A=790 mm Power equipment





Serie_763

illuminance



luminous intensity

