MACH LED PLUS.forty - MLAL 12 S 113161000-00660033



ENGINEER OF LIGHT.

LED



fitted with work equipment connected load power consumption luminous flux luminous efficacy light distribution Beam Angle light color color rendering index (CRI) system of protection class of protection technology usage luminaire body lamp cover weight (net) mains supply

design fastening dimension special features without 20-28V; DC approx. 5 W approx. 490 lm approx. 98 lm/W direct, narrow-angled beam 40°/80° neutral white, approx. 5000 K > 80 IP 67 |||switchable external aluminium, anodized, aluminium colored anodized screen, clear approx. 0.3 kg (0.66 lb) built-in plug M12 4-pole A-coded mounted version L-angle, clamp A=190 mm (7.48 in) angle of illumination 40°

M12 4-pole A-coded

illuminance Comment: d=100cm





