
Flexible-tube luminaire ROCIA.focus RFF 600/850/DS





113184000-00680272



CE 🚇







light source work equipment connected load power consumption luminous flux luminous efficiency light distribution beam angle colour temperature colour temperatur color rendering index (CRI) chromaticity tolerance LED glare control luminance (L65) unified glare rating (4H 8H) system of protection class of protection technology operation housing cover mains lead fastening special features

LED without 12-28V AC and 12-40V DC env. 8 W approx. 600 lm approx. 75 lm/W direct, narrow-angled beam 10° neutral white approx. 5.000 K >= 80 < 4 SDCM screen <= 4000 cd/m² <= 16 IP 67 Ш switchable; continuously dimmable push button aluminium; anodised; black glass screen approx. 3,2 m; with free stranded wires table clamp (accessory); wall bracket (accessory); screw-down flange Spot with a 10° angle of radiation

Flexible-tube luminaire ROCIA.focus RFF 600/850/DS

113184000-00680272



Φ: 600 lm	E 0°	
C0-C180: 9°		
0.25 m	126 <mark>82</mark> 6 lx	0.039 m
0.50 m	31 <mark>706</mark> lx	0.078 m
0.75 m	1 <mark>4092</mark> x	0.12 m
1.00 m	7927 Ix	0.16 m