



**light source**  
**work equipment**  
**connected load**  
**power consumption**  
**luminous flux**  
**luminous efficiency**  
**light distribution**  
**beam angle**  
**colour temperature**  
**colour temperatur**  
**color rendering index (CRI)**  
**chromaticity tolerance LED**  
**glare control**  
**luminance (L65)**  
**unified glare rating (4H 8H)**  
**system of protection**  
**class of protection**  
**technology**  
**operation**  
**housing**  
**cover**  
**mains lead**  
**fastening**  
**accessory**  
**special features**

LED  
without  
12-28V AC and 12-40V DC  
env. 8 W  
approx. 600 lm  
approx. 75 lm/W  
direct, narrow-angled beam  
10°  
neutral white  
approx. 5.000 K  
≥ 80  
< 4 SDCM  
screen  
≤ 4000 cd/m<sup>2</sup>  
≤ 16  
IP 67  
III  
switchable  
external  
aluminium; anodised; black  
glass screen  
approx. 3,7 m; with free stranded wires  
wall bracket (accessory); screw-down flange;  
magnetic base (accessory)  
ballast  
Spot with a 10° angle of radiation

Pivoting-head luminaire ROCIA.focus  
RFJ 600/850/S

113185000-00668613

