

Surface-mounted luminaire LINURA.edge LEA 600/850/S

114035000-00801346









light sourceLEDwork equipmentwithoutconnected load22-26 V, DCpower consumptionenv. 6 Wluminous fluxapprox. 630 lmluminous efficiencyapprox. 105 lm/W

light distributiondirectbeam angle89° / 97°colour temperatureneutral whitecolour temperaturapprox. 5.000 K

color rendering index (CRI)>= 80chromaticity tolerance LED< 4 SDCM</th>glare controlscreensystem of protectionIP 54class of protectionIII

technology switchable operation external

housing aluminium/plastic; anodised, painted; aluminium

coloured anodised Acrylic satine

coverAcrylic satineweight (net)env. 0,150 kg

mains leadbuilt-in plug; M12-A-5designmounted version

fastening bracket

dimension A=335mm,Cmin=290mm,Cmax=320mm