

# Datasheet

## Moulded Momentary Foot Switch

RS Stock No. 116-906



<b>Degree of protection</b>	IP20
<b>Materials of Construction</b>	Corrosion proof reinforced polymeric.
<b>Colour</b>	Dark Grey.
<b>Cable Connection</b>	Adjustable strain relief clamp accommodates a wide range of cable sizes.
<b>Contact Action</b>	SPDT Momentary.
<b>Electrical Rating</b>	15A 125-250V a.c, 0.375kW 125-250V a.c.
<b>Features &amp; Benefits</b>	Flame retardant. Raised ribs on operating cover ensures good grip. Non-skid base pads.
<b>Weight</b>	0.1kg
<b>Size</b>	(See below)

