11

## **Insulation Strippers**










11 08 160 ★ 1000 V ▲ → WW

- for single, multiple and fine-stranded conductors with plastic or rubber insulation of a maximum 13/64" diameter. Also suitable for 7 AWG wire.
- easy adjustment to the required diameter of solid or stranded wire with knurled screw and lock nut
- Special tool steel; forged, oil-hardened









Prismatic blade:
The red area is cut over four surfaces. Works with highly-elastic materials also.

Product Number	<b>←→</b> inch	<b>←→</b> mm		Pliers	Head	Handles	S Ø inch	tripping c		AWG	∆ ∆ Ounces
11 01 160	6 1/4	160	MM	black atramentized	polished	plastic coated	13/64	5.0	10.0	7	4.6
11 02 160	6 1/4	160	MM	black atramentized	polished	with multi-component grips	13/64	5.0	10.0	7	5.8
11 08 160	6 1/4	160	<b>≙</b> 1000 V <b>△€ ///</b>	black atramentized	polished	insulated with multi-component grips, VDE-tested	13/64	5.0	10.0	7	5.9