Data Sheet

HUBER+SUHNER

Coaxial Cable Connector 11_BNC-50-3-54/103_N

Description

Straight cable plug

Interface standards IEC 60169-8_MIL-STD-348A/301_CECC 22120



Technical Data

Electrical Data		
Impedance	50 Ω	
Interface frequency max.	4 GHz	
Mechanical Data		
Centre contact	soldered	
Outer contact	soldered	
Weight	0.0096 kg	
Environmental Data		
Operating temperature	-65 °C to 165 °C	
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant	
Material Data		
Piece Parts	Material	Surface Plating
Centre contact	Brass	Gold Plating (Nickel underplated)
Outer contact	Brass	Silver Plating
Body	Brass	Silver Plating
Insulator	PFA / PTFE	
Coupling nut	Brass	SUCOPLATE (R) Plating
Gasket	VMQ (Silicone rubber)	
Related Documents		
Outline drawing	DOU-00006656	
Catalogue drawing	DOU-00006658	

Outline drawingDOU-00006656Catalogue drawingDOU-00006658Assembly instructionDOC-000180227

Ordering Information

Single package

11_BNC-50-3-54/103_NE

Additional Information

Suitable cables

EZ_141_TP_M17, SUCOFORM_141

HUBER+SUHNER is certified according to ISO 9001, ISO 14001, ISO/TS 16949 and IRIS

www.hubersuhner.com

Waiver: It is exclusively in written agreements that we provide our customers with warrants and representations as to the technical specifications and/or the fitness for any particular purpose. The facts and figures contained herein are carefully compiled to the best of our knowledge, but they are intended for general information purposes only.