

Coaxial Cable Connector 11_N-50-2-1/133_N

Description

Straight cable plug

Interface standards

IEC 61169-16_MIL-STD-348A/304_CECC 22210



Technical Data

Electrical Data

Impedance	50 Ω
Interface frequency max.	11 GHz

Mechanical Data

Centre contact	soldered
Outer contact	clamped
Weight	0.0352 kg

Environmental Data

Operating temperature	-65 °C to 165 °C
2011/65/EU, RoHS	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Brass	Gold Plating (Nickel underplated)
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Coupling nut	Brass	SUCOPLATE (R) Plating
Gasket	VMQ (Silicone rubber)	

Related Documents

Outline drawing	DOU-00006961
Catalogue drawing	DOU-00006959
Assembly instruction	DOC-0000177464

Ordering Information

Single package	11_N-50-2-1/133_NE
----------------	--------------------

Additional Information

Suitable cables	RG_316_/U, RG_188_A/U, RG_174_/U
-----------------	----------------------------------