

Coaxial Cable Connector 11_N-75-4-3/133_N

Description

Straight cable plug

Interface standards

IEC 60169-16_MIL-STD-348A/304_CECC 22210



Technical Data

Electrical Data

Impedance	75 Ω
Interface frequency max.	1.5 GHz

Mechanical Data

Centre contact	soldered
Outer contact	clamped
Weight	0.0341 kg

Environmental Data

Operating temperature	-65 °C to 165 °C
2011/65/EU, RoHS	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Brass	Gold Plating (Nickel underplated)
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Coupling nut	Brass	SUCOPLATE (R) Plating
Gasket	VMQ (Silicone rubber)	

Related Documents

Outline drawing	DOU-00006123
Catalogue drawing	DOU-00006125
Assembly instruction	DOC-0000179335

Ordering Information

Single package	11_N-75-4-3/133_NE
----------------	--------------------

Additional Information

Suitable cables	RG_59_B/U, GX_04273, G_04273-12, GX_04273-12
-----------------	--