

Datasheet

Stock No: 121-7802

RS Pro Sockets for Miniature Power Relay



Specifications:

- Comes with metal retaining clip
- Suitable for 121-7795, 121-7796, 121-7797, 121-7798, 121-7799, 121-7800, 121-7801

RS Stock No	121-7802	
Characteristics		
Nominal Load	Current	10A
	Voltage	300V
Dielectric Strength	2500 V/S	
Max. Tightening Torque	1Nm	
Wire Size	20-14 AWG / 0.5-2.5mm ²	
Ambient Temperature	-40~+85°C	
Unit Weight	45g	
Accessories	Metal Clip, ID tag	
Certification		

