

#### **FEATURES**

- Glass reinforced polyester (GRP) case providing protection to IP44
- 110V centre tapped to earth (CTE) secondary winding
- 10amp thermal magnetic trip (hand resettable) reducing the chance of overload
- 2x 16A 110V Sockets
- Thermal overload protection
- Intermittent rating: maximum ration for operating load
- 2 metre input mains lead with 13A UK domestic plug

# RS PRO, 3.3kVA Portable Isolation Transformer, 230V ac, 2 x 16A

RS Stock No.: 122-6705



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

## Safety Site Transformers



#### **Product Description**

This safety transformer from our own RS PRO brand is high quality, UK manufactured to BSEN (British Standard European Norm) 61588 and fully compliant with reduced low voltage regulations.

#### **General Specifications**

Туре	Portable Tool Isolation Transformer
Enclosure	GRP - Colour yellow
Applications	Isolation, transmission, distribution and utilization of alternating current electric power, Increasing low AC voltages at high current or decreasing high AC voltages at low current in electric power applications, and for coupling stages of signal processing circuits

#### **Electrical Specifications**

Power Rating	3.3kVA
Primary Voltage Rating	230V ac
Secondary Voltage Rating	110 (55V-0V-55V)V
Output Current	2 x 16A
Minimum Operating Frequency	50Hz
Maximum Operating Frequency	60Hz
Plug Type	BS 1363
Socket Type	BS EN 60309
Thermal Cutout	10AMP



### **Mechanical Specifications**

Mounting Type	Stand Alone
Dimensions	195mm x 195mm x 265mm
Length	195mm
Width	195mm
Depth	265mm
Weight	18kg

#### **Protection Category**


IP Rating	IP44

#### **Approvals**

Compliance/Certifications	RoHS Directive 2011/65/EU
Standards Met	BS EN 61558, BS EN 61558-20-23, BS EN 60529







Page 4 of 4