



Datasheet

RS Pro Heat Gun, 220-240V, 2000W

ENGLISH

RS Stock No 124-5158

Specification

- Overall size in 25x 9.1x25.5cm
- Material of housing: plastic
- Rate voltage 220-240v
- Rate frequency 60hz
- Rate power:2000w
- Temperature
- I: 350°C,250l/min
- li: 550°C,550l/min
- Cable length: 1.8m
- VDE power cord
- VDE plug
- Include accessories:
- 4pcs nozzle (reflector nozzle, glass protector nozzle, cone nozzle, fishtail nozzle)
- 1pc scraper—plastic handle
- One convertor (vde to bs)
- Each set in blow mould case



Features and Benefits

- Shrinking of shrink down tubing, solder connectors and solder terminals, packaging and electrical components.
- Deforming of articles made from acrylic, PVC, and polystyrene, tubing, plates and profiles, as well as moist woods.
- Welding of thermoplastic polymer, flooring materials of PVC and linoleum, PVC-coated fabric, tarpaulins and foils.
- Soldering of tin, special silver solder, SMD elements, cable lugs, and for loosening soldered connections.
- Paint removal—Removal of old and even thick coatings of oil paint, varnish and synthetic plaster.
- Drying of colour shade samples, filter, adhesives, construction joints and stucco forms.
- Joining adhesives—Large-surface gluing with contact adhesives, activation of pressure-sensitive adhesives, acceleration of bonding processes, releasing of bonding points as well as releasing or bonding of edge bond or venee.
- Defrosting of icy stairs and steps, door locks, trunk lids, car doors or water pipes, as well as for defrosting refrigerators and ice boxes.
- Disinfection—With hot air of 600°C , you can quickly rid animal sties/stables of bacteria. Woodworm infestation can be controlled (Caution: Danger of fire! Do not heat up the wooden surface excessively).