

FEATURES

- Rugged construction
- Universal XLR panel cut out
- No special tooling required
- Front or back panel mounting

RS PRO USB Connector, Panel Mount, Socket 2.0 A, B, Straight- Dual Port

RS Stock No.: 124-6393



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

USB Connectors



Product Description

A range of RS PRO USB gender changer sockets in rugged XLR housings. The USB connectors convert from USB 2 A to B or USB 2 B to A. Designed to accommodate USB2 data feeds into professional broadcasting, audio and lighting applications. Housings are constructed from nickel plated zinc and are available in self-coloured or black options. Suitable for front or rear panel mounting.

Available in this Range - 2.0 USB Connector, Receptacle

- 862-1579 USB A to B Socket self-colour
- 862-1573 USB B to A Socket self-colour
- 124-6392 USB A to B Socket Black metal
- 124-6393 USB B to A Socket Black metal

General Specifications

Gender	Female
Mounting Type	Panel Mount
USB Type	A, B
USB Version	2.0
Body Orientation	Straight
Number of Ports	2
Colour	Black
Insert Material	ABS
Frame Material	Nickel plated zinc die cast
Shell Material	Nickel plated steel
Termination Method	USB2 A/B plug

Electrical Specifications

Current Rating	1.5A
Voltage Rating	30Vac
Contact Resistance	30mΩ
Insulation Resistance	20MΩ min
Dielectric withstanding voltage	500Vac



Operation Environment Specifications

Minimum Operating Temperature	-20.0°C
Maximum Operating Temperature	50°C

Protection Category

IP Rating	IP67

Approvals


Compliance/Certifications	RoHS
---------------------------	------






USB Connectors








124-6392 – USB A→B Gender change feedthrough socket, Black





124-6393 – USB2 B→A Gender change feedthrough socket, Black



USB Connectors



