



ENGLISH

Datasheet

RS Pro Diagonal Cutters

Stock No: 125-3070



Product Details

RS Pro G12 Series insulated diagonal cutter. Ideal for working up to 1000 V ac or 1500 V dc. Suitable for cutting soft and hard wire.

- Special tool steel
- Chrome finish
- Duo Tech soft grip handles
- VDE Approved
- ISO 5749
- G12 Series

Specification

Cutting Capacity Hard Wire	2.5	mm
Cutting Capacity Soft Wire	2.5	mm
Jaw Length	24	mm
Material	Steel	
Maximum Cutting Capacity	2.5 (Hard Wire), 2.5 (Soft Wire)	mm
Model Number	G12-18-0180	
Overall Length	180 mm	
Type	Diagonal	
VDE/1000V Approved	Yes	