

LED Downlights



VT-26101

HIGHLIGHTS :

WATTS



10

EQ. WATTS



90

LUMINOUS



1200

BEAM ANGLE



120

Item No	: VT-26101
SKU Code	: 1271
Watts	: 10
EQ Watts	: 90
Base / holder	: RECESSED
Voltage	: AC:100-277V,50/60Hz
Lumen(lm)	: 1200
Color Temperature	: 4500k
Beam Angle	: 120
Commercial type	: ROUND
PF	: >0.5
LED Chip Type	: COB
CRI	: >80
Energy rating label	: A++
Certification	: CE,EMC,ROHS
IP Rating Protection Class	: IP20

Body type	: PKW
Dimmable	: No
Life Time	: >20,000 Hours
Operation Temperature	: -25 ~50°C
EAN code	: 3800157611930
Unit size	: D:135x71mm
Cutting size	: D:120mm
Packing details	: 27
Unit cbm	: 0.002791

PRODUCT FEATURES

- Innumerable styles & Elegant appearance
- Non - Flickering
- No UV Radiation
- Premium Quality Power Driver with lowest power factor saver & high RA
- Varied finishes with strong die cast Aluminium body
- Residences, Showrooms, Hotels & Boutiques etc.

[CLICK HERE](#)
FOR OTHER RELATED CERTIFICATES 