

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1300530004](#)
Status: **Active**
Overview: Brad Industrial Ethernet Solutions
Description: Brad RJ-Lnxx Direct PCB Mount Ethernet Receptacle, 1" - 14 UNC Threads

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

| | |
|----------------|--|
| Product Family | Industrial Receptacles |
| Series | 130053 |
| IP Rating | IP67 |
| NEMA Rating | NEMA 6 |
| Overview | Brad Industrial Ethernet Solutions |
| Product Name | Brad, RJ-Lnxx |
| Type | PCB Mount |
| UPC | 78678846636 |

Physical

| | |
|-------------------------------|-----------------|
| Coupling Type | External Thread |
| Gender | Female |
| Keyway | None |
| Length | N/A |
| Material - Component | ABS |
| Mounting Thread Size | 1" - 14 UNC |
| Net Weight | 120.000/g |
| Orientation | Straight |
| Panel Mount | N/A |
| Poles | N/A |
| Temperature Range - Operating | -20° to +80°C |
| Wire Size AWG | N/A |
| Wire/Cable Type | N/A |

Electrical

| | |
|-------------------------------|---------|
| Current - Maximum per Contact | 1.5A |
| Voltage - Maximum | 125V DC |

Material Info

| | |
|--------------------|----------|
| Engineering Number | ENPR1FF5 |
|--------------------|----------|

Reference - Drawing Numbers

| | |
|---------------|-------------------|
| Sales Drawing | SD-130053-001-001 |
|---------------|-------------------|



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2021)4569-DC (8
July 2021)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[130053 Series](#)