

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1300640187](#)
Status: **Active**
Overview: BradPower Cordsets and Receptacles
Description: BradPower D-Size (1 3/8"-M35) Double-Ended Cordset, 4 Poles, Male (Straight) to Female (Straight), 10 AWG, Gray PVC Cable, 2.0m (6.56') Length

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

UL E258922

General

Product Family	Industrial Cordsets
Series	130064
Connector End A	BradPower D-Size (1 3/8"-M35)
Connector End B	BradPower D-Size (1 3/8"-M35)
IP Rating	IP67
Material - Contact	Copper Alloy
Overview	BradPower Cordsets and Receptacles
Product Name	BradPower D-Size
Protocol	EtherNet
Region	Europe
Type	Double Ended
UPC	78678855746

Physical

Cable Diameter	5.08mm (.200")
Cable Length	2.0m (6.56')
Color - Cable Jacket	Gray
Coupling Style	Threaded
Gender	Female-Male
Keyway	Single
LED Indicator	No
Material - Cable Jacket	PVC
Material - Connector Body	TPE
Material - Coupling Nut	Anodized Aluminum
Material - Plating Mating	Gold
Net Weight	1324.490/g
Orientation	Straight to Straight
Poles	4
Temperature Range - Operating	-20° to +90°C
Wire Size AWG	10
Wire/Cable Type	STOOW, TC-ER Direct Burial

Electrical


Current - Maximum per Contact	32.0A
Voltage - Maximum	600V AC/DC

Material Info

Engineering Number	CC4030A48M020
--------------------	---------------

Reference - Drawing Numbers

Sales Drawing	SD-130064-065-001
---------------	-------------------



EU ELV

Not Relevant

EU RoHS

Compliant with Exemption 6(c)

REACH SVHC

Contained Per -
D(2021)10043-DC (17
Jan 2022)

Lead

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

50 Image

Not Relevant

Not Contained

Search Parts in this Series

130064 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION