



ENGLISH

Datasheet
Stock No. 1368567
Digital Ultrasonic Cleaner 6500ml



Specifications:

Ultrasonic Frequency	40,000 Hz
Material	Stainless Steel SUS304
Tank Capacity	6.5 L
Timer	1~30min adjustable
Heater	0~80°C adjustable
Power Supply	AC 200 ~ 240V, 50 Hz
Ultrasonic Power	180W, 3 transducers
Heating Power	200 W

27/04/2017

Tank Size **300 x 150 x 150 mm (L x W x H)**
Unit Size **325 x 180 x 280 mm (L x W x H)**
Accessories **Tray**
With IEC power cord

Features:

- 1. Stainless steel tank has resistance to wear and long work life.**
- 2. Tank capacity:6.5L(1.7gallon), with digital timer & heater control**
- 3. With Stainless steel basket**
- 4. Use just tap water, or industrial alcohol and solvent cleaner for more higher cleaning requirement**
- 5. Industrial control chip microcontroller . Flexible circuit boards control, more secure & stable**
- 6. Temperature tunable from 0°C to 80°C**
- 7. with drainage**
- 8. Certifications : CE & RoHS & ISO9001.**

Applications:

electronic factory
jewelry factory
chemical lab
dental clinic
household
restaurant
repair shop