

Data sheet**Jokari dismantle tool**

Page 1/4

P/N

140302-01-E

EAN 4250184150107

2021/08/30

Illustrations

See enlarged drawings at the end of document

Product specification

- for fast and precise stripping of data cables
- with adjustable stop



P | Cabling

Data sheet Jokari dismantle tool

Page 2/4

P/N
140302-01-E
EAN 4250184150107
2021/08/30

Technical Data

General Data

| | |
|--------|----------------------|
| Design | Cable stripping tool |
| Color | white |

Materials and material properties

| | |
|------|-----------|
| RoHS | compliant |
|------|-----------|

Classifications

| | |
|----------|----------|
| ETIM 5.0 | EC000766 |
| ETIM 6.0 | EC000766 |
| ETIM 7.0 | EC000163 |
| ETIM 8.0 | EC000163 |

Packing details

| | |
|---------------------------------|------------------------------------|
| Type of packaging | 1 pc(s) / plastic bag |
| Packaging unit - Weight (gram) | 48 g |
| Packaging unit - Weight (pound) | 0.11 lb |
| Packaging dimension | 160 mm x 100 mm x 380 mm |
| Packaging dimension | 6.299 in. x 3.937 in. x 14.961 in. |



Accessories from

| P/N | Designation |
|----------------|---|
| 1308406030000 | 'BTR Cat.6 AWG24 U/UTP 4P FR-PVC' |
| 1308406032132 | BTR GC250 23 Cat.6 U/UTP 4P LSHF 1000m |
| 1308406032140 | MC GC400 SL23 Cat.6 U/UTP LSHF 1000 ft, class E _{ca} |
| 1308406032141 | MC GC400 SL23 Cat.6 U/UTP LSHF 1640 ft, class E _{ca} |
| 1308406032142 | MC GC400 SL23 Cat.6 U/UTP LSHF 3280 ft, class E _{ca} |
| 1308406A32141 | MC GC500 Z2F23 Cat.6 _A U/UTP 4P LSHF 1640 ft, class E _{ca} |
| 1308416A3P34M | MC GC500 23 Cat.6 _A F/UTP CMP |
| 1308416A3R34M | MC GC500 23 Cat.6 _A F/UTP CMR |
| 1308426A3P000 | BTR NETCOM E-DAT cable Cat.6A S-FTP CMP |
| 1308426A3R000 | BTR NETCOM E-DAT cable Cat.6A S-FTP CMR |
| 130842702P000 | BTR NETCOM E-DAT cable Cat.7 S-FTP CMP |
| 130842702R000 | BTR NETCOM E-DAT cable Cat.7 S-FTP CMR |
| 1308427032133M | BTR GC1000 HS23 Cat.7 S/FTP 2x4P LSHF |
| 130842703213M | BTR GC1000 HS23 Cat.7 S/FTP 4P LSHF |
| 1308427032141 | MC GC1000 plus23 Cat.7 S/FTP 4P LSHF 1640 ft, class E _{ca} |
| 1308427032142 | MC GC1000 plus23 Cat.7 S/FTP 4P LSHF 3280 ft, class E _{ca} |
| 1308427032143 | MC GC1000 plus23 Cat.7 S/FTP 2x4P LSHF 1640 ft, class E _{ca} |
| 1308427032144 | MC GC1000 plus23 Cat.7 S/FTP 2x4P LSHF, class E _{ca} |
| 130842703214M | MC GC1000 plus23 Cat.7 S/FTP 4P LSHF, class E _{ca} |
| 1308427034132M | BTR GC1000 pro23 Cat.7 S/FTP 4P LSHF-FR |
| 1308427034141 | MC GC1000 pro23 Cat.7 S/FTP 4P LSHF-FR 1640 ft, class D _{ca} s2 d1 a1 |
| 1308427034142 | MC GC1000 pro23 Cat.7 S/FTP 4P LSHF-FR 3280 ft, class D _{ca} s2 d1 a1 |
| 130842703414M | MC GC1000 pro23 Cat.7 S/FTP 4P LSHF-FR, class D _{ca} s2 d1 a1 |
| 1308427038101 | MC IC1000 PUR 23/1 Cat.7 S/FTP 4P 1640 ft, class F _{ca} |
| 1308427038102 | MC IC1000 PUR 23/1 Cat.7 S/FTP 4P 3280 ft, class F _{ca} |
| 130842703810M | MC IC1000 PUR 23/1 Cat.7 S/FTP 4P, class F _{ca} |
| 1308427A32132M | BTR GC1200 HS22 Cat.7A S/FTP 4P LSHF-FR |
| 1308427A32133M | BTR GC1200 HS22 Cat.7A S/FTP 2x4P LSHF-FR |
| 1308427A34132M | BTR GC1500 pro22 Cat.7A S/FTP 4P LSHF-FR |
| 1308427A34141 | MC GC1500 pro22 Cat.7 _A S/FTP 4P LSHF-FR 1640 ft, class D _{ca} s2 d1 a1 |
| 1308427A34142 | MC GC1500 pro22 Cat.7 _A S/FTP 4P LSHF-FR 3280 ft, class D _{ca} s2 d1 a1 |

Accessories from

| | |
|---------------|---|
| 1308427A3414M | MC GC1500 pro22 Cat.7 _A S/FTP 4P LSHF-FR, class D _{ca} s2 d1 a1 |
| 1308427A34241 | MC GC1200 pro22 Cat.7 _A S/FTP 4P LSHF-FR 1640 ft, class D _{ca} s2 d1 a1 |
| 1308427A34242 | MC GC1200 pro22 Cat.7 _A S/FTP 4P LSHF-FR 3280 ft, class D _{ca} s2 d1 a1 |
| 1308427A34243 | MC GC1200 pro22 Cat.7 _A S/FTP 2x4P LSHF-FR 1640 ft, class D _{ca} s2 d1 a1 |
| 1308427A34244 | MC GC1200 pro22 Cat.7 _A S/FTP 2x4P LSHF-FR, class D _{ca} s2 d1 a1 |
| 1308427A3424M | MC GC1200 pro22 Cat.7 _A S/FTP 4P LSHF-FR, class D _{ca} s2 d1 a1 |
| 1308427B34141 | MC GC1300 pro22 Cat.7 _A S/FTP 4P LSHF-FR 1640 ft, class D _{ca} s2 d2 a1 |
| 1308427B34142 | MC GC1300 pro22 Cat.7 _A S/FTP 4P LSHF-FR 3280 ft, class D _{ca} s2 d2 a1 |
| 1308427B34143 | MC GC1300 pro22 Cat.7 _A S/FTP 2x4P LSHF-FR 1640 ft, class D _{ca} s2 d2 a1 |
| 1308427B34144 | MC GC1300 pro22 Cat.7 _A S/FTP 2x4P LSHF-FR, class D _{ca} s2 d2 a1 |
| 1308427B34145 | MC GC1300 pro22 Cat.7 _A S/FTP 4P LSHF-FR 328 ft, class D _{ca} s2 d2 a1 |
| 1308427B3414M | MC GC1300 pro22 Cat.7 _A S/FTP 4P LSHF-FR, class D _{ca} s2 d2 a1 |
| 1308436A32141 | MC GC600 F1 23 Cat.6 _A U/FTP 4P LSHF 1640 ft, class E _{ca} |
| 1308436A32142 | MC GC600 F1 23 Cat.6 _A U/FTP 4P LSHF 3280 ft, class E _{ca} |
| 1308436A3214M | MC GC600 F1 23 Cat.6 _A U/FTP 4P LSHF, class E _{ca} |

