

CONNECT

P | Cabling

We realize ideas

Page 1/6


P/N 1509QKJA0010-E EAN 4251394625485

> 2023/06/22 Version: H

Data sheet OpDAT FAST[™] Hybrid connector kit LC APC OS2 10 pieces for cables

Illustrations





See enlarged drawings at the end of document

Product specification

- Field-attachable fiber optic connector for single-mode technology
- · with hybrid technology: refractive index gel plus opto-elastomer guarantee very good and constant optical values
- no polishing, no gluing during assembly on site
- simple, easy to learn, fast and cost-effective installation in less than two minutes
- Available with connector types LC and SC for singlemode (UPC and APC)
- plug kits for FO fibers with Ø 0.25 and Ø 0.9 mm
- plug kits for fibre optic cables with Ø 2.0 and Ø 3.0 mm
- the plug can be assembled up to three times
- · every plug has a serial number, so that traceability is possible at any time
- Included in the scope of delivery depending on the variant:
- a maintenance-free separator (Cleaver). It provides an oblique cut so that high return loss values are achieved. The Cleaver can be used up to 200 times.
- · a cable assembly kit for easy cable assembly
- · a fiber guide for easy insertion of the fiber into the connector
- · fields of application:
- for FTTH and FITH connections, repairs in the field, in areas which are difficult to access or limited in space and for direct mounting on components
- · Versions for fibers: 10 pieces without tools / 20 or 100 pieces with Cleaver and fibre guide
- Variants for cables: 10 pieces without tools / 20 or 100 pieces with Cleaver, cable assembly set and fibre guide







We realize ideas

Data sheet OpDAT FASTTM Hybrid connector kit LC APC OS2 10 pieces for cables

Page 2/6

P/N 1509QKJA0010-E EAN 4251394625485

> 2023/06/22 Version: H

General Data	
Fields of application	structured building cabling Consolidation points office areas fiber to the desk Distributed building services data center
Mechanical measurement according to MICE	M1
Ingress measurement according to MICE	I1
Climatic measurement according to MICE	C1
Electromagnetic measurement according to MICE	E3
Design	plug, field assambly
Transmission technology	Fiber optic
Color	green
Dimensions	
Dimension (L x W x H)	57 mm x 4.47 mm x 4.47 mm
Dimension (L x W x H)	2.244 in. x 0.176 in. x 0.176 in.
Mode type of the fiber	Singlemode
Shape	APC (Angled Physical Contact)
Connections/interfaces	
Connector technology interface 1	mechanical splice, fibre cut diagonally
Connector technology interface 2	LC
Single fibre diameter (min max.)	
Single fibre diameter	3 mm
Cable access/outlet	180°
Electrical characteristics	
Insertion loss	0,2 bis 0,5 dB
Return loss	min. 60 dB







We realize ideas

Data sheet OpDAT FASTTM Hybrid connector kit LC APC OS2 10 pieces for cables

Page 3/6

P/N 1509QKJA0010-E EAN 4251394625485

> 2023/06/22 Version: H

		3/06/22 sion: F
Technical Data	vei	SIOH. F
Mechanical data		
Connector type	simplex	
Mounting method	snap-in function	
Life - Number of mating cycles	min. 500	
Materials and material properties		
Material - Housing	Plastics	
Material - Cable boot	elastomer, flame-retardant and halogen free	
Material - Ferrule	Ceramic	
Material - Dust protection	elastomer, flame-retardant and halogen free	
Halogen free	yes	
RoHS	compliant	
Environmental conditions		
Temperature (min max.)		
Temperature - Storage °C	-25 °C - 70 °C	
Temperature - Storage °F	-13 °F - 158 °F	
Temperature - Operating °C	-25 °C - 70 °C	
Temperature - Operating °F	-13 °F - 158 °F	
Standards/Regulations		
FO connector interfaces	IEC 61754-20 / ANSI/TIA-604-10-A	
Fibre optic connector interfaces	IEC 61754-20	
Classifications		
ETIM 7.0	EC001122	
ETIM 8.0	EC001122	
ETIM 9.0	EC001122	
Packing details		
Type of packaging	10 pc(s) / box	









We realize ideas

Data sheet
OpDAT FASTTM Hybrid connector kit LC APC OS2
10 pieces for cables

Page 4/6

P/N 1509QKJA0010-E EAN 4251394625485

> 2023/06/22 Version: H

Accessories

P/N	Designation
150800200-E	Fibre optic tool Bag





We realize ideas

Data sheet
OpDAT FASTTM Hybrid connector kit LC APC OS2
10 pieces for cables

Page 5/6

P/N 1509QKJA0010-E EAN 4251394625485

> 2023/06/22 Version: H

Accessories from

P/N	Designation
14040000-E	MCO IP69k protective housing for outdoor use, set for exposed installation
14040010-E	MCO IP69k Protective housing for outdoor use, set with mounting bracket
14040100-E	MCO IP69k Protective housing for outdoor use, set wall/ housing bushing







We realize ideas

Data sheet
OpDAT FASTTM Hybrid connector kit LC APC OS2
10 pieces for cables

Page 6/6

P/N 1509QKJA0010-E EAN 4251394625485

> 2023/06/22 Version: H

Illustrations

Dimensional drawing

